

# BLUEMARK ID - Printer



1003334

<https://www.phoenixcontact.com/us/products/1003334>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Monochrome printer with UV inkjet technology and integrated "MARKING system app" identification software. 7" color touch display for printing plastic labels in UC, UCT, US, and UM format, as well as metal labels.

## Your advantages

- Intuitive and time-saving operation using integrated marking software and a graphical user interface
- Marking that is instantly wipe-resistant, so that marking materials are ready for immediate use
- Rapid marking of plastic and metal labels for marking terminals, conductors, cables, devices, and plants
- Scalable print resolution between standard (300 dpi) and HD printing (600 dpi)
- Environmentally-sound, emission-free high-speed printer with modern UV LED technology
- The printer detects the direction of the inserted sheets and automatically rotates printing 180° if required



## Commercial data

Item number	1003334
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG01
Product key	BG1211
GTIN	4055626471075
Weight per piece (including packing)	32 kg
Weight per piece (excluding packing)	27.5 kg
Customs tariff number	84433210
Country of origin	DE

1003334

<https://www.phoenixcontact.com/us/products/1003334>

## Technical data

### Product properties

Product type	Marking system
--------------	----------------

### Marking

Identification technology	UV LED technology
---------------------------	-------------------

### Device properties

Operating system	MS Windows 7 (32/64-bit), MS Windows 8 (32/64-bit), MS Windows 8.1 (32/64-bit), MS Windows 10 (32/64-bit), MS Windows 11 (32/64-bit)
------------------	--

### Electrical properties

#### Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

### Dimensions

Width	523 mm
Height	340 mm
Length	675 mm

### Material specifications

Material Plastic signs	UC
	UCT
	US
	UM

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	5 °C ... 35 °C
---------------------------------	----------------

1003334

<https://www.phoenixcontact.com/us/products/1003334>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1003334>



**EAC**

Approval ID: KZ 27978



**EAC-RoHS**

Approval ID: RU D-DE.HB49.B.00023

**UAE-RoHS**

Approval ID: 13774\_E22-04-033961



**KC**

Approval ID: R-R-PCK-1002329



**IECEE CB Scheme**

Approval ID: REP095544



**cCSAus**

Approval ID: 80261925

1003334

<https://www.phoenixcontact.com/us/products/1003334>

## Classifications

### ECLASS

ECLASS-13.0	19140103
ECLASS-15.0	19140103

### ETIM

ETIM 10.0	EC001684
-----------	----------

### UNSPSC

UNSPSC 21.0	43212100
-------------	----------

1003334

<https://www.phoenixcontact.com/us/products/1003334>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 6(c), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5151b77e-12fc-4411-a28c-34b331fc62b0

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)