

PML-GHS100 (13X13)R - Hazardous substances label



1014289

<https://www.phoenixcontact.com/us/products/1014289>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Hazardous substances label, Roll, Mixed color, unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2: Diamond, mounting type: adhesive, Number of individual labels: 500, text field height: 13 mm, text field width: 13 mm

Your advantages

- The color preprinted PML-GHS ... hazardous substance labels without symbols allow you to create custom hazard notices. A wide range of symbols are available in the PROJECT complete software.
- The markers conform to the GHS international standard
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences

Commercial data

Item number	1014289
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG21
Product key	BG2611
GTIN	4046356787048
Weight per piece (including packing)	88.1 g
Weight per piece (excluding packing)	88.1 g
Customs tariff number	39199080
Country of origin	DE

Technical data

Product properties

Product type	Plant marker
Area of application	Hazardous substance labels
	Hazardous substance labeling according to CLP/GHS regulation
Type	Diamond

Marking

Number of individual labels	500
Number of individual labels per row	3
Printing	Diamond
Identification technology	Thermal transfer

Dimensions

Width	18.37 mm
Height	18.37 mm
Depth	0.08 mm

Text field

Text field width	13 mm
Text field height	13 mm

Material specifications

Color	multicolored (RAL -)
	red (RAL 3001)
	white (RAL 9010)
Base element material	Polyester
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

PML-GHS100 (13X13)R - Hazardous substances label



1014289

<https://www.phoenixcontact.com/us/products/1014289>

Mounting

Mounting type
adhesive

1014289

<https://www.phoenixcontact.com/us/products/1014289>

Classifications

ECLASS

ECLASS-13.0	40200202
ECLASS-15.0	40200202

ETIM

ETIM 10.0	EC001777
-----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

PML-GHS100 (13X13)R - Hazardous substances label



1014289

<https://www.phoenixcontact.com/us/products/1014289>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com