

# ES/KMK 3-GB - Insert strip

1005088

<https://www.phoenixcontact.com/us/products/1005088>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert strip, Sheet, white (RAL 9010), unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: insert, Number of individual labels: 52, text field height: 17.2 mm, text field width: 39.75 mm



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1005088       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BG12          |
| Product key                          | BG2312        |
| GTIN                                 | 4017918012397 |
| Weight per piece (including packing) | 10.25 g       |
| Weight per piece (excluding packing) | 10.029 g      |
| Customs tariff number                | 48025890      |
| Country of origin                    | DE            |

## Technical data

### Notes

|         |   |
|---------|---|
| General | Print image may vary depending on laser printer |
|---------|---|

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Terminal marker |
|--------------|-----------------|

### Marking

|                                     |    |
|-------------------------------------|----|
| Number of individual labels         | 52 |
| Number of individual labels per row | 4  |

### Dimensions

|        |          |
|--------|----------|
| Width  | 39.55 mm |
| Height | 17.20 mm |
| Depth  | 0.17 mm  |

### Text field

|                   |          |
|-------------------|----------|
| Text field width  | 39.75 mm |
| Text field height | 17.2 mm  |

### Material specifications

|                       |                                |
|-----------------------|--------------------------------|
| Color                 | white (RAL 9010)               |
| Base element material | Polyester                      |
| Components            | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|   |                   |
|---|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C             |
| Recommended humidity (storage/transport)            | 50 %              |

#### Wipe resistance of inscriptions

|               |  |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03           |
|               | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

### Mounting

|               |        |
|---------------|--------|
| Mounting type | insert |
|---------------|--------|

# ES/KMK 3-GB - Insert strip

1005088

<https://www.phoenixcontact.com/us/products/1005088>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281106 |
| ECLASS-15.0 | 27281106 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131700 |
|-------------|----------|

# ES/KMK 3-GB - Insert strip



1005088

<https://www.phoenixcontact.com/us/products/1005088>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)