

# PKB 140X3,6 - Cable tie

1005460

<https://www.phoenixcontact.com/us/products/1005460>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable tie, dimensions: L x W, 140 x 3.6 mm, color: transparent



## Commercial data

Item number	1005460
Packing unit	1,000 pc
Sales key	BE07
Product key	BE7131
GTIN	4017918012533
Weight per piece (including packing)	0.65 g
Weight per piece (excluding packing)	0.65 g
Customs tariff number	39269097
Country of origin	SG

# PKB 140X3,6 - Cable tie



1005460

<https://www.phoenixcontact.com/us/products/1005460>

## Technical data

### Product properties

Product type	Cable tie
Tensile strength GRP	130 N

### Dimensions

Width	3.6 mm
Length	140 mm

### Material specifications

Color	transparent
Material	PA
Flammability rating according to UL 94	V2
Components	halogen-free

### Cable/line

Tensile strength	130 N
------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 60 °C
Resistance to UV radiation	yes

### Mounting

Mounting type	Cannot be removed
---------------	-------------------

# PKB 140X3,6 - Cable tie



1005460

<https://www.phoenixcontact.com/us/products/1005460>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)