

# FL BT EPA 2 - Wireless module

1005869

<https://www.phoenixcontact.com/us/products/1005869>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bluetooth/Ethernet wireless module, 2.1+EDR/4.0, PAN P2P, internal antenna, IP65, 9 V DC ...  
30 V DC, M12 connection, WEB, AT-commands and mode button

## Your advantages

- Bluetooth wireless modul
- Protocol-transparent communication on Layer 2
- Degree of protection IP65
- Integrated antenna



## Commercial data

Item number	1005869
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN26
Product key	DNN2B1
GTIN	4055626476087
Weight per piece (including packing)	152.6 g
Weight per piece (excluding packing)	105 g
Customs tariff number	85176200
Country of origin	LT

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Wireless module
Application	Ethernet
Type	Stand-alone

#### Wireless card

Number	1
Assembly note	Permanently installed

### Electrical properties

Maximum power dissipation for nominal condition	1.7 W
---	-------

#### Supply: Module electronics

Connection technology	M12 connector
Connection method	M12 connector, A-coded (male)
Supply voltage	24 V DC
Supply voltage range	9 V DC ... 30 V DC
Supply current	typ. 36 mA (at 24 V DC)
Current consumption	max. 190 mA (at 9 V DC)

### Input data

#### Digital:

Number of inputs	1
------------------	---

### Connection data

#### Power supply input

Connection method	M12 connector, A-coded (male)
pluggable	yes

### Interfaces

#### Ethernet

Interface	Ethernet
Number	1
Connection method	M12 connector, D-coded (female)

#### Functions

Configuration	Web interface, MODE button, AT commands (TCP/IP), SSC
---------------	---

# FL BT EPA 2 - Wireless module



1005869

<https://www.phoenixcontact.com/us/products/1005869>

Security	PIN
	Non-discoverable
Wireless licenses	Europe, USA, Canada, additional countries in the e-shop
	RED (Radio Equipment Directive)
	FCC 47 CFR part 15, subpart B
Country support	Belgium
	Bulgaria
	Denmark
	Germany
	Estonia
	Finland
	France
	Greece
	Great Britain
	Ireland
	Iceland
	Italy
	Canada
	Croatia
	Latvia
	Liechtenstein
	Lithuania
	Luxembourg
	Malta
	Netherlands
	Norway
	Austria
	Poland
	Portugal
	Romania
	Sweden
	Switzerland
	Slovakia
	Slovenia
	Spain
	Czech Republic
	Hungary
USA	
Cyprus (rep.)	
Japan	
Cyprus (rep.)	
10/100 Mbps Ethernet	
Number of interfaces	1

# FL BT EPA 2 - Wireless module



1005869

<https://www.phoenixcontact.com/us/products/1005869>

Connection method	M12 connector, D-coded (female)
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)

## Wireless

Designation	Bluetooth
Antenna connection method	(Internal)
Frequency range	2.402 GHz ... 2.48 GHz (Bluetooth)
Frequency band	2.4 GHz
Wireless standard	Bluetooth 2.1 + EDR
Transmission power	max. 10 dBm
Number of wireless interfaces	1 Bluetooth 2.1+EDR, Bluetooth LE 4.0
Wireless modules that can be connected	1
Profiles supported	PAN (NAP, PANU) GATT (central)

## Dimensions

Width	67.8 mm
Height	92.7 mm
Depth	33.2 mm
Note on dimensions	Without M12 connections

## Material specifications

Color (Housing)	black (RAL 9005)
-----------------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 93 % (non-condensing)
Permissible humidity (storage/transport)	non-condensing

### Mechanical test

Shock in accordance with EN 60068-2-27/IEC 60068-2-27	3g, 11 ms half-sine shock pulse
Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	5 - 8.4 Hz= ±3.5 mm; 8.4 - 40.7 Hz = 1g; 40.7 - 57Hz= ±0.15 mm; 57 - 500 Hz= 2g

## EMC data

### Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

### Electromagnetic HF field

# FL BT EPA 2 - Wireless module



1005869

<https://www.phoenixcontact.com/us/products/1005869>

Standards/regulations	EN 61000-4-3
-----------------------	--------------

## Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

## Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

## Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

## Emitted interference

Standards/regulations	EN 55022
-----------------------	----------

## Mounting

Mounting type	Panel mounting
Assembly note	Internal antenna

# FL BT EPA 2 - Wireless module




1005869

<https://www.phoenixcontact.com/us/products/1005869>


## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1005869>

 **UL Listed**  
Approval ID: E238705

 **cUL Listed**  
Approval ID: E238705

 **cUL Listed**  
Approval ID: E196811

 **UL Listed**  
Approval ID: E196811

# FL BT EPA 2 - Wireless module



1005869

<https://www.phoenixcontact.com/us/products/1005869>

## Classifications

### ECLASS

ECLASS-15.0	19170101
ECLASS-13.0	19170101

### ETIM

ETIM 10.0	EC000515
-----------	----------

### UNSPSC

UNSPSC 21.0	43201400
-------------	----------

# FL BT EPA 2 - Wireless module



1005869

<https://www.phoenixcontact.com/us/products/1005869>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	26.66 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)