

PMM (EX40)R CUS - Magnetic label



1014327

<https://www.phoenixcontact.com/us/products/1014327>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Magnetic label, Roll, can be ordered: by line, white (RAL 9010), labeled according to customer specifications, mounting type: magnetic adhesion, Number of individual labels: 1, text field height: 40 mm, text field width: 15000 mm

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1014327 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BG8151 |
| GTIN | 4046356786317 |
| Weight per piece (including packing) | 1.99 g |
| Weight per piece (excluding packing) | 1.99 g |
| Country of origin | PL |

PMM (EX40)R CUS - Magnetic label



1014327

<https://www.phoenixcontact.com/us/products/1014327>

Technical data

Product properties

| | |
|---------------------|-----------------------|
| Product type | Plant marker |
| Area of application | Warehousing/logistics |
| Product property | magnetic |

Marking

| | |
|-------------------------------------|----------------|
| Number of individual labels | 1 |
| Number of individual labels per row | 1 |
| Identification technology | Thermotransfer |

Dimensions

| | |
|--------|----------|
| Width | 50.00 mm |
| Height | 40.00 mm |
| Depth | 0.60 mm |
| Length | 15000 mm |

Text field

| | |
|-------------------|----------|
| Text field width | 15000 mm |
| Text field height | 40 mm |

Material specifications

| | |
|-----------------------|------------------|
| Color | white (RAL 9010) |
| Material | Magnetic tape |
| Coating | Polyester foil |
| Base element material | Magnetic tape |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -30 °C ... 55 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Procedure | Artificial irradiation. |

Wipe resistance of inscriptions

| | |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

PMM (EX40)R CUS - Magnetic label



1014327

<https://www.phoenixcontact.com/us/products/1014327>

Mounting

| | |
|---------------|-------------------|
| Mounting type | magnetic adhesion |
|---------------|-------------------|

PMM (EX40)R CUS - Magnetic label



1014327

<https://www.phoenixcontact.com/us/products/1014327>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281104 |
| ECLASS-15.0 | 27281104 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

PMM (EX40)R CUS - Magnetic label



1014327

<https://www.phoenixcontact.com/us/products/1014327>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com