

# UT 2,5-3L BK - Multi-level terminal block

1007631

<https://www.phoenixcontact.com/us/products/1007631>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multi-level terminal block, nom. voltage: 500 V, nominal current: 19 A, connection method: Screw connection, Rated cross section: 2.5 mm<sup>2</sup>, cross section: 0.14 mm<sup>2</sup> - 4 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: black

## Your advantages

- Globally recognized: Internationally proven screw connection
- Maintenance-free and vibration-resistant thanks to the patented Reakdyn principle
- Space savings and flexibility with the connection of two identical conductors
- Long-term stable connections with the use of high-quality materials
- Low self-heating due to high contact forces
- Maximum efficiency in the smallest space - thanks to integrated level bridging, the connections are connected across levels
- High space savings thanks to the compact integration of two separate circuits in a single terminal block

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1007631       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE01          |
| Product key                          | BE1115        |
| GTIN                                 | 4055626479460 |
| Weight per piece (including packing) | 25.44 g       |
| Weight per piece (excluding packing) | 23.9 g        |
| Customs tariff number                | 85369010      |
| Country of origin                    | PL            |

# UT 2,5-3L BK - Multi-level terminal block



1007631

<https://www.phoenixcontact.com/us/products/1007631>

## Technical data

### Product properties

|                       |                            |
|-----------------------|----------------------------|
| Product type          | Multi-level terminal block |
| Product family        | UT                         |
| Number of positions   | 1                          |
| Number of connections | 6                          |
| Number of rows        | 3                          |
| Potentials            | 3                          |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 6 kV   |
| Maximum power dissipation for nominal condition | 0.77 W |

### Connection data

|                                 |                     |
|---------------------------------|---------------------|
| Number of connections per level | 2                   |
| Nominal cross section           | 2.5 mm <sup>2</sup> |
| Rated cross section AWG         | 12                  |

### Level 1+2+3

|   |  |
|---|--|
| Connection method   | Screw connection                             |
| Screw thread  | M3   |
| Tightening torque   | 0.5 ... 0.6 Nm                               |
| Stripping length  | 9 mm   |
| Internal cylindrical gage   | A3   |
| Connection in acc. with standard  | IEC 60947-7-1                                |
| Conductor cross-section rigid   | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Cross section AWG   | 26 ... 12 (converted acc. to IEC)            |
| Conductor cross-section flexible  | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section, flexible [AWG]   | 26 ... 12 (converted acc. to IEC)            |
| Conductor cross-section flexible ultrasound-compressed                                    | 0.34 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section, flexible [AWG] ultrasound-compressed                             | 22 ... 12 (converted acc. to IEC)            |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| 2 conductors with same cross section, rigid   | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| 2 conductors with same cross section, flexible  | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>  |
| Nominal cross section   | 2.5 mm <sup>2</sup>                          |

# UT 2,5-3L BK - Multi-level terminal block



1007631

<https://www.phoenixcontact.com/us/products/1007631>

|                      |  |
|----------------------|--|
| Nominal current      | 19 A (with a 2.5 mm <sup>2</sup> conductor cross-section)  |
| Maximum load current | 24 A (in case of a 4 mm <sup>2</sup> conductor cross-section, the maximum load current must not be exceeded by the total current of all connected conductors.) |
| Nominal voltage      | 500 V  |
| Note                 | Note: Product releases, connection cross sections and notes on connecting aluminum cables can be found in the download area.                                   |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 5.2 mm  |
| End cover width    | 2.2 mm  |
| Height             | 90 mm   |
| Depth on NS 35/7,5 | 77.5 mm |
| Depth on NS 35/15  | 85 mm   |

## Material specifications

|  |                  |
|--|------------------|
| Color  | black (RAL 9005) |
| Flammability rating according to UL 94                           | V0               |
| Insulating material group  | I                |
| Insulating material  | PA               |
| Static insulating material application in cold                   | -60 °C           |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C           |
| Fire protection for rail vehicles (DIN EN 45545-2) R22           | HL 1 - HL 3      |
| Fire protection for rail vehicles (DIN EN 45545-2) R23           | HL 1 - HL 3      |
| Fire protection for rail vehicles (DIN EN 45545-2) R24           | HL 1 - HL 3      |
| Fire protection for rail vehicles (DIN EN 45545-2) R26           | HL 1 - HL 3      |
| Surface flammability NFPA 130 (ASTM E 162)                       | passed           |
| Specific optical density of smoke NFPA 130 (ASTM E 662)          | passed           |
| Smoke gas toxicity NFPA 130 (SMP 800C)                           | passed           |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Environmental and real-life conditions

### Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)  |
| Ambient temperature (assembly)           | -5 °C ... 70 °C  |
| Ambient temperature (actuation)          | -5 °C ... 70 °C  |
| Permissible humidity (operation)         | 20 % ... 90 %  |
| Permissible humidity (storage/transport) | 30 % ... 70 %  |

# UT 2,5-3L BK - Multi-level terminal block



1007631

<https://www.phoenixcontact.com/us/products/1007631>

## Standards and regulations


|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

## Drawings

Circuit diagram



# UT 2,5-3L BK - Multi-level terminal block



1007631

<https://www.phoenixcontact.com/us/products/1007631>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1007631>



**EAC**

Approval ID: KZ7500651131219505



**cULus Recognized**

Approval ID: E60425

|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| B |                       |                       |                   |                             |
|   | 300 V                 | 20 A                  | 26 - 12           | -                           |
| C |                       |                       |                   |                             |
|   | 300 V                 | 20 A                  | 26 - 12           | -                           |
| D |                       |                       |                   |                             |
|   | 600 V                 | 5 A                   | 26 - 12           | -                           |



**CSA**

Approval ID: 13631

|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| B |                       |                       |                   |                             |
|   | 300 V                 | 20 A                  | 26 - 12           | -                           |
| C |                       |                       |                   |                             |
|   | 300 V                 | 20 A                  | 26 - 12           | -                           |
| D |                       |                       |                   |                             |
|   | 600 V                 | 5 A                   | 26 - 12           | -                           |

# UT 2,5-3L BK - Multi-level terminal block



1007631

<https://www.phoenixcontact.com/us/products/1007631>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250102 |
| ECLASS-15.0 | 27250102 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000897 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UT 2,5-3L BK - Multi-level terminal block



1007631

<https://www.phoenixcontact.com/us/products/1007631>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | dfbc14f8-e42d-43ae-a826-ec940891b0f1 |

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.085 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)