

# PSR-MC73-5NO-1DO-24DC-SC - Safety relays



1015533

<https://www.phoenixcontact.com/us/products/1015533>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety relay for emergency stop, safety doors, light grids up to SIL 3, Cat. 4, PL e, 1- or 2-channel operation, cross-circuit detection, can be retriggered, off-/on delay of 0.2 s to 300 s, 5 enabling current paths,  $U_S = 24$  V DC, plug-in screw terminal block

## Product description

The safety relay PSR-MC73 is designed to monitor various items of safety equipment, e.g., emergency stop, safety doors, or light grids. Despite its compact overall width of 22.5 mm, the device offers the option of setting release or on delays with high accuracy in the range from 0.2 s to 300 s. In addition, the delay time can be reset using the adjustable retrigger function when the safety function is demanded.

## Your advantages

- Up to Cat. 4/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with EN IEC 62061
- Low housing width of only 22.5mm
- 1 or 2-channel control
- 2 enabling current paths (adjustable, retriggerable release or on delay), 1 digital signal output
- Adjustable delay time from 0.2 s ... 300 s



## Commercial data

Item number	1015533
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN01
Product key	DNA181
GTIN	4055626496740
Weight per piece (including packing)	245.4 g

# PSR-MC73-5NO-1DO-24DC-SC - Safety relays



1015533

<https://www.phoenixcontact.com/us/products/1015533>

Weight per piece (excluding packing)	223.1 g
Customs tariff number	85371098
Country of origin	DE

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Safety relays
Product family	PSRcompact
Application	Emergency stop
	Safety door
	Light grid
Control	1 and 2 channel
Relay type	Electromechanical relay with force-guided contacts in accordance with IEC/EN 61810-3

#### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

#### Times

Typical response time	< 50 ms (automatic start)
	< 50 ms (manual, monitored start)
Typ. starting time with $U_S$	500 ms (with $U_S$ when controlled via A1)
Typical release time	< 25 ms (when controlled via S12 and S22 (only for undelayed contacts))
	< 10 ms (when controlled via A1; applicative deactivation via A1/A2 is not permitted)
Delay time range	0.2 s ... 300 s $\pm 5$ % (can be set for 47/48, 57/58)
Restart time	< 1 s (Boot time)
Recovery time	500 ms (following demand of the safety function)
	100 ms (Availability time after activating the sensor circuit during manual start)
Start pulse length	min. 500 ms (manual start)

### Electrical properties

Maximum power dissipation for nominal condition	9.91 W (at $U_S = 30$ V, $I_L^2 = 144$ A <sup>2</sup> )
Nominal operating mode	100% operating factor
Rated insulation voltage	250 V AC
Rated surge voltage/insulation	See data sheet, section "Insulation coordination".

#### Supply

Designation	A1/A2
Rated control circuit supply voltage $U_S$	24 V DC -20 % / +25 %
Rated control supply current $I_S$	typ. 80 mA

# PSR-MC73-5NO-1DO-24DC-SC - Safety relays



1015533

<https://www.phoenixcontact.com/us/products/1015533>

Power consumption at $U_S$	typ. 1.92 W
Inrush current	typ. 28 A ( $\Delta t = 30 \mu s$ at $U_S$ )
Filter time	1 ms (For the logic. At A1 in the event of voltage dips at $U_S$ )
Protective circuit	Serial protection against polarity reversal
	Suppressor diode

## Input data

Digital: Sensor circuit (S12, S22)

Description of the input	safety-related sensor inputs
Number of inputs	2
Input voltage range "0" signal	0 V DC ... 5 V DC
Input voltage range "1" signal	11 V DC ... 30 V DC
Input current range "0" signal	0 mA ... 2 mA
Inrush current	< 11 mA (typ. with $U_S$ )
Filter time	max. 3 ms (Test pulse width of low test pulses)
	min. 21 ms (Test pulse rate for low test pulse)
Concurrency	$\infty$
Limit frequency	min. 0 Hz
	max. 1 Hz
Max. permissible overall conductor resistance	150 $\Omega$
Protective circuit	Varistor
Current consumption	< 4.5 mA (typ. with $U_S$ )

Digital: Start circuit (S34)

Description of the input	non-safety-related
Number of inputs	1
Input voltage range "0" signal	0 V DC ... 5 V DC
Input voltage range "1" signal	11 V DC ... 30 V DC
Input current range "0" signal	0 mA ... 2 mA
Inrush current	< 8.6 mA (typ. with $U_S$ )
Filter time	max. 1 ms (Test pulse width of low test pulses)
	min. 21 ms (Test pulse rate for low test pulse)
Limit frequency	min. 0 Hz
	max. 1 Hz
Max. permissible overall conductor resistance	150 $\Omega$
Protective circuit	Varistor
Current consumption	< 3.2 mA (typ. with $U_S$ )

## Output data

Relay: Enabling current paths (13/14, 23/24/34, 47/48, 57/58)

Output description	2 N/O contacts each in series, safety-related, floating
Number of outputs	3 (undelayed: 13/14, 23/24/34)
	2 (delayed: 47/48, 57/58)
Contact switching type	5 enabling current paths

# PSR-MC73-5NO-1DO-24DC-SC - Safety relays



1015533

<https://www.phoenixcontact.com/us/products/1015533>

Contact material	AgCuNi +0.2 µm ... 0.4 µm Au / AgSnO <sub>2</sub> +0.2 µm Au
Switching voltage	min. 12 V AC/DC
	max. 250 V AC/DC
Switching power	min. 60 mW
Inrush current	min. 5 mA
	max. 6 A
Switching capacity	4 A (24 V (DC13))
	3 A (230 V (AC 15))
Limiting continuous current	6 A
Sq. Total current	144 A <sup>2</sup> (observe derating)
Switching frequency	0.1 Hz (depending on the set delay time)
Mechanical service life	10x 10 <sup>6</sup> cycles
Output fuse	6 A gL/gG
	4 A gL/gG (for low-demand applications)

## Signal: M1

Output description	PNP
	non-safety-related
Number of outputs	1
Voltage	approx. 23 V DC (U <sub>S</sub> - 1 V)
Current	max. 100 mA
Maximum inrush current	500 mA (Δt = 100 ms at U <sub>S</sub> )
Ohmic load	min. 192 Ω (max. 100 mA)
Switching frequency	0.1 Hz (depending on the set delay time)
Protective circuit	Suppressor diode
Short-circuit protection	Yes
Discharging circuit	no

## Clock: S11, S21

Output description	PNP
	non-safety-related
Number of outputs	2
Voltage	corresponds to U <sub>S</sub>
Current	max. 100 mA
Maximum inrush current	500 mA (Δt = 100 ms at U <sub>S</sub> )
Protective circuit	Suppressor diode
Short-circuit protection	Yes
Discharging circuit	no

## Connection data

### Connection technology

pluggable	yes
-----------	-----

### Conductor connection

Connection method	Screw connection
-------------------	------------------

# PSR-MC73-5NO-1DO-24DC-SC - Safety relays



1015533

<https://www.phoenixcontact.com/us/products/1015533>

Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm
Screw thread	M3
Tightening torque	0.5 Nm ... 0.6 Nm

## Signaling

Status display	4 x LED (green, yellow, red)
Operating voltage display	1 x LED (green, yellow, red)

## Dimensions

Width	22.5 mm
Height	112.7 mm
Depth	111.7 mm

## Material specifications

Color (Housing)	yellow (RAL 1018)
Housing material	PA

## Characteristics

### Safety data

Stop category (EN 60204-1)	0 (Undelayed contacts)
Stop category	1 (delayed contacts)

### Safety data: EN ISO 13849

Performance level (PL)	e (4 A DC13; 3 A AC15; 8760 switching cycles/year)
------------------------	--

### Safety data: IEC 61508 - High demand

Safety Integrity Level (SIL)	3
------------------------------	---

### Safety data: IEC 61508 - Low demand

Safety Integrity Level (SIL)	3
------------------------------	---

### Safety data: EN IEC 62061

Safety Integrity Level (SIL)	3
------------------------------	---

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Ambient temperature (operation)	-35 °C ... 55 °C (observe derating) -35 °C ... 60 °C (mounted in the horizontal mounting position with ≥ 10 mm spacing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Maximum altitude	≤ 2000 m (Above sea level)

# PSR-MC73-5NO-1DO-24DC-SC - Safety relays



1015533

<https://www.phoenixcontact.com/us/products/1015533>

Max. permissible humidity (storage/transport)	75 % (on average, 85% infrequently, non-condensing)
Max. permissible relative humidity (operation)	75 % (on average, 85% infrequently, non-condensing)
Shock	10g (operation), 15g (transport)
Vibration (operation)	10 Hz ... 150 Hz, 2g

## Mounting

Mounting type	DIN rail mounting
Assembly note	See derating curve
Mounting position	vertical or horizontal

# PSR-MC73-5NO-1DO-24DC-SC - Safety relays




1015533


<https://www.phoenixcontact.com/us/products/1015533>

## Drawings

Circuit diagram



Block diagram



Block diagram

# PSR-MC73-5NO-1DO-24DC-SC - Safety relays



1015533

<https://www.phoenixcontact.com/us/products/1015533>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1015533>



**cULus Listed**

Approval ID: E140324



**Functional Safety**

Approval ID: 01/205/5486.02/24

# PSR-MC73-5NO-1DO-24DC-SC - Safety relays



1015533

<https://www.phoenixcontact.com/us/products/1015533>

## Classifications

### ECLASS

ECLASS-13.0	27371819
ECLASS-15.0	27371819

### ETIM

ETIM 10.0	EC001449
-----------	----------

### UNSPSC

UNSPSC 21.0	39122200
-------------	----------

1015533

<https://www.phoenixcontact.com/us/products/1015533>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)
SCIP	3bb6380a-3506-4e07-921f-eefa21a54032

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)