

HBUS 35,6-16P-2S OT BK - Housing half shell



1012037

<https://www.phoenixcontact.com/us/products/1012037>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing for use in distribution boards in accordance with DIN 43880, Upper part, height: 13.6 mm, color: black (similar RAL 9005)



Commercial data

Item number	1012037
Packing unit	10 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	ACHBBA
GTIN	4055626488837
Weight per piece (including packing)	3 g
Weight per piece (excluding packing)	1.597 g
Country of origin	DE

HBUS 35,6-16P-2S OT BK - Housing half shell



1012037

<https://www.phoenixcontact.com/us/products/1012037>

Technical data

Product properties

Product type	Housing half shells
Housing type	DIN rail housing for use in distribution boards in accordance with DIN 43880
Housing series	BC
Number of positions	16

Dimensions

Height	13.6 mm
Length	37.1 mm
Horizontal pitch	2 Div.

Material specifications

Color (Housing half-shell)	black (RAL 9005)
Material Housing half-shell	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (dependent on the derating curve)
---------------------------------	---

HBUS 35,6-16P-2S OT BK - Housing half shell



1012037

<https://www.phoenixcontact.com/us/products/1012037>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1012037>



UL Recognized

Approval ID: E240868

HBUS 35,6-16P-2S OT BK - Housing half shell



1012037

<https://www.phoenixcontact.com/us/products/1012037>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HBUS 35,6-16P-2S OT BK - Housing half shell



1012037

<https://www.phoenixcontact.com/us/products/1012037>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.017 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com