CDC-MP 1,5-2,5-R - Crimp contact

1016659

https://www.phoenixcontact.com/us/products/1016659

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, nominal current: 12 A, contact connection type: Socket, connection method: Crimp connection, contact surface: Tin, type of packaging: Belt, product range: CDC-MP

Commercial data

Item number	1016659
Packing unit	3,000 pc
Minimum order quantity	3,000 pc
Note	Made to order (non-returnable)
Sales key	AA03
Product key	AACDCA
GTIN	4055626498645
Weight per piece (including packing)	2.22 g
Weight per piece (excluding packing)	0.21 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

Note on application	The crimp contacts may only be processed with approved crimping tools.
Order information:	You can find ordering information for the approved crimping tool for automated conductor connections in the installation instructions in the Downloads section.
Note regarding documentation	The crimp heights depend on the crimping tool used. You can find the values in the tool documentation.

Product properties

Product type	Crimp contact
Product family	CDC-MP

Connection data

Connection method	Crimp connection
Contact connection type	Socket
Stripping length	4 mm
Conductor cross-section flexible	1.5 mm² ... 2.5 mm²
Conductor cross-section AWG	16 ... 14

Material specifications

Contact surface	Tin Sn
Contact surface material	Tin
Metal surface terminal point (top layer)	Tin (2 - 4 µm Sn)
Metal surface contact area (top layer)	Tin (2 - 4 µm Sn)
Surface characteristics	hot-dip tin-plated
Contact material	Cu alloy

Electrical properties

Nominal current I_N	12 A

Packaging specifications

Type of packaging	Belt

Classifications

ECLASS

ECLASS-13.0	27460403
ECLASS-15.0	27460403

ETIM

ETIM 10.0	EC000796

UNSPSC

UNSPSC 21.0	39121500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com