

PABA RD/15 - Insert label

1013944

<https://www.phoenixcontact.com/us/products/1013944>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insert label, Strip, red (RAL 3001), unmarked, can be labeled with: CMS-P1-PLOTTER, cable diameter range: 0.6 ... 50 mm, mounting type: slide-on, Number of individual labels: 20, text field height: 4 mm, text field width: 15 mm

Commercial data

Item number	1013944
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BG20
Product key	BG2213
GTIN	4017918014124
Weight per piece (including packing)	4.294 g
Weight per piece (excluding packing)	4.294 g
Customs tariff number	39269097
Country of origin	CN

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	20
Number of individual labels per row	1

Dimensions

Width	15 mm
Length	4 mm

Text field

Text field width	15 mm
Text field height	4 mm

Material specifications

Color	red (RAL 3001)
Material	ABS
Flammability rating according to UL 94	V0

Cable/line

External cable diameter	0.6 mm ... 50 mm
-------------------------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-15 °C ... 65 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

Scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

PABA RD/15 - Insert label



1013944

<https://www.phoenixcontact.com/us/products/1013944>

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

PABA RD/15 - Insert label



1013944

<https://www.phoenixcontact.com/us/products/1013944>

Standards and regulations

Wipe resistance

DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type

slide-on

PABA RD/15 - Insert label


1013944

<https://www.phoenixcontact.com/us/products/1013944>



Drawings

Dimensional drawing



PABA RD/15 - Insert label



1013944

<https://www.phoenixcontact.com/us/products/1013944>

Classifications

ECLASS

ECLASS-13.0

27281102

ETIM

ETIM 9.0

EC001530

UNSPSC

UNSPSC 21.0

39131500

PABA RD/15 - Insert label



1013944

<https://www.phoenixcontact.com/us/products/1013944>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.033 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com