

FOC-17S12-LCD6-GF02/0,6 - Distributor cable



1018563

<https://www.phoenixcontact.com/us/products/1018563>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Distributor cable, degree of protection: IP20, cable length: 0.6 m



Your advantages

- Compact design with MT ferrule
- Proven screw locking mechanism for reliable connection between the field and device side
- For extreme ambient conditions
- 1000 hours salt spray test
- Ideal for use under harsh conditions
- Fast mounting thanks to preassembled fiber-optic cable

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1018563 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB15 |
| Product key | ABNHBB |
| GTIN | 4055626503486 |
| Weight per piece (including packing) | 97.3 g |
| Weight per piece (excluding packing) | 83.83 g |
| Customs tariff number | 85367000 |
| Country of origin | CN |

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Data cable preassembled |
| Number of positions | 12 |
| No. of conductors | 12 |

Electrical properties

| | |
|---------------------|-----------------------|
| Attenuation | typ. 0.35 dB |
| Transmission medium | Multi-mode fiberglass |

Mechanical properties

| | |
|---------------------------------------|---------------|
| Tensile strength short-term/long-term | 500 N / 200 N |
|---------------------------------------|---------------|

Material specifications

| | |
|------------------------|-------------------|
| Ferrule material | Zirconia ceramics |
| Outer sheath, material | LSFH |

Connector

Connection 1

| | |
|----------------------|-------------------------|
| Locking type | Screw locking mechanism |
| Material | Stainless steel |
| Degree of protection | IP68 (IEC 60529) |

Connection 2

| | |
|----------------------|------------------|
| Locking type | Push Pull |
| Handle color | beige |
| Material | Plastic |
| Degree of protection | IP20 (IEC 60529) |

Cable/line

| | |
|---------------------------------------|------------------------------|
| Cable length | 0.6 m |
| Cable weight | 8.30 kg/km |
| Cable type | Multimode fiberglass |
| Cable type | Fan out |
| Cable abbreviation | 12-.../(ZN)H-...30 |
| External cable diameter | 7 mm |
| Outer sheath, material | LSFH |
| External sheath, color | orange |
| Wire diameter incl. insulation | 250 µm |
| Tensile strength short-term/long-term | 500 N / 200 N |
| Lateral pressure short term | 500.00 N/cm |
| Lateral pressure, long-term | 100.00 N/cm |
| Halogen-free | complying with IEC 60754-1/2 |

FOC-17S12-LCD6-GF02/0,6 - Distributor cable



1018563

<https://www.phoenixcontact.com/us/products/1018563>

FO cable

| | |
|---------------------|----------------------------------|
| Number of fibers | 12 |
| Fiber | 62.5/125 µm OM1 |
| Fiber type | Multimode fiberglass 62.5/125 µm |
| Transmission medium | Multi-mode fiberglass |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -20 °C ... 70 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Ambient temperature (assembly) | -10 °C ... 50 °C |

FOC-17S12-LCD6-GF02/0,6 - Distributor cable



1018563

<https://www.phoenixcontact.com/us/products/1018563>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27061004 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

FOC-17S12-LCD6-GF02/0,6 - Distributor cable



1018563

<https://www.phoenixcontact.com/us/products/1018563>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com