

US-PML-W100 (25X25) CUS - Warning label



1014128

<https://www.phoenixcontact.com/us/products/1014128>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Warning label, can be ordered: by card, Mixed color, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 24, text field height: 25 mm, text field width: 25 mm



Your advantages

- UniSheet - stick-on warning labels, marked according to customer specifications
- Suitable for indoor and outdoor use
- The warning labels conform to the ISO 7010 international standard
- Highly flexible, soft PVC label that adapts well to uneven surfaces

Commercial data

Item number	1014128
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8159
GTIN	4046356786690
Weight per piece (including packing)	5.1 g
Weight per piece (excluding packing)	5.1 g
Country of origin	PL

US-PML-W100 (25X25) CUS - Warning label



1014128

<https://www.phoenixcontact.com/us/products/1014128>

Technical data

Product properties

Product type	Plant marker
Area of application	Warning labels
	Warning identification according to ISO 7010
Type	Triangle

Marking

Number of individual labels	24
Identification technology	Thermotransfer

Dimensions

Width	23.08 mm
Height	20.34 mm
Depth	0.08 mm

Text field

Text field width	25 mm
Text field height	25 mm

Material specifications

Foil strength	60 µm
Adhesive strength	25 µm
Adhesive	Acrylic
Color	multicolored (RAL -)
	yellow (RAL 1018)
	black (RAL 9005)
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 %

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

US-PML-W100 (25X25) CUS - Warning label



1014128

<https://www.phoenixcontact.com/us/products/1014128>

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Mounting

Mounting type	adhesive
---------------	----------

US-PML-W100 (25X25) CUS - Warning label



1014128

<https://www.phoenixcontact.com/us/products/1014128>

Classifications

ECLASS

ECLASS-15.0	40200203
ECLASS-13.0	40200203

ETIM

ETIM 10.0	EC001777
-----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

US-PML-W100 (25X25) CUS - Warning label



1014128

<https://www.phoenixcontact.com/us/products/1014128>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com