

# PML-P110 (D50) - Prohibition sign

1014211

<https://www.phoenixcontact.com/us/products/1014211>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Prohibition sign, Sheet, labeled: No food, mounting type: adhesive, diameter: 50 mm, Number of individual labels: 3, text field height: 50 mm, text field width: 50 mm

## Your advantages

- Stick-on prohibition signs, preprinted with symbol
- Suitable for indoor and outdoor use
- The prohibition signs conform to the ISO 7010 international standard

## Commercial data

Item number	1014211
Packing unit	5 pc
Minimum order quantity	1 pc
Product key	BG2624
GTIN	4046356785068
Weight per piece (including packing)	5.8 g
Weight per piece (excluding packing)	5.8 g
Country of origin	DE

# PML-P110 (D50) - Prohibition sign



1014211

<https://www.phoenixcontact.com/us/products/1014211>

## Technical data

### Product properties

Product type	Plant marker
Area of application	Prohibition signs
	Prohibition marking according to ISO 7010
Type	circular

### Marking

Number of individual labels	3
Printing	No food

### Dimensions

Width	50 mm
Height	50 mm

### Text field

Text field width	50 mm
Text field height	50 mm

### Material specifications

Foil strength	60 µm
Adhesive strength	25 µm
Adhesive	Acrylic
Color	red/white
Material	PVC
Components	Silicone-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### Scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

#### Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
---------------	----------------------------------

# PML-P110 (D50) - Prohibition sign



1014211

<https://www.phoenixcontact.com/us/products/1014211>

Result	Test passed
--------	-------------

## UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

## Temperature storage

Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb
Duration	96 h
Temperature for testing	120 °C

## Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

## Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. - ]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S

# PML-P110 (D50) - Prohibition sign



1014211

<https://www.phoenixcontact.com/us/products/1014211>

Cycles	2
--------	---

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	adhesive
---------------	----------

# PML-P110 (D50) - Prohibition sign



1014211

<https://www.phoenixcontact.com/us/products/1014211>

## Classifications

### ECLASS

ECLASS-13.0

40200202

### ETIM

ETIM 9.0

EC001777

### UNSPSC

UNSPSC 21.0

55121700

# PML-P110 (D50) - Prohibition sign



1014211

<https://www.phoenixcontact.com/us/products/1014211>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)