

PML-T105 (26X280)R CUS - Pipeline marker



1014257

<https://www.phoenixcontact.com/us/products/1014257>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pipeline marker, can be ordered: by line, Mixed color, labeled according to customer specifications: Non-flammable gases, mounting type: adhesive, diameter: 0 mm, text field height: 280 mm, text field width: 26 mm

Your advantages

- Stick-on pipeline markers, unmarked
- Suitable for indoor and outdoor use
- Pipeline marking according to DIN 2403
- In combination with the PML-GHS hazardous substances labels, marking which conforms to the Ordinance on Hazardous Substances (GefStoffV) can be applied
- High adhesive strength
- Finely perforated arrowheads enable the arrowheads which are not required to be easily removed
- High temperature resistance
- Group 5 (non-combustible gases)

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1014257 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BG8151 |
| GTIN | 4046356784535 |
| Weight per piece (including packing) | 5.58 g |
| Weight per piece (excluding packing) | 5.58 g |
| Country of origin | PL |

Technical data

Product properties

| | |
|---------------------|---|
| Product type | Plant marker |
| Area of application | Pipeline labels |
| | Pipeline identification according to DIN 2403 |
| Type | Rectangle |

Marking

| | |
|-------------------------------------|---------------------|
| Number of individual labels per row | 3 |
| Printing | Non-flammable gases |

Dimensions

| | |
|--------|-----------|
| Width | 280.00 mm |
| Height | 26.00 mm |
| Depth | 0.08 mm |
| Length | 26 mm |

Text field

| | |
|-------------------|--------|
| Text field width | 26 mm |
| Text field height | 280 mm |

Material specifications

| | |
|-----------------------|----------------------|
| Foil strength | 50 µm |
| Adhesive strength | 24 µm |
| Adhesive | Acrylic |
| Color | multicolored (RAL -) |
| | yellow (RAL 1018) |
| | black (RAL 9005) |
| Material | Polyester |
| Base element material | Polyester |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 150 °C |
| Recommended ambient temperature (storage/transport) | 20 °C |
| Recommended humidity (storage/transport) | 40 % ... 50 % (Storage in a dry and dark place in the original packaging is recommended) |

Scratch resistance

| | |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements | ≥ 5 N |
| Result | Test passed |

Tesafilm test

PML-T105 (26X280)R CUS - Pipeline marker



1014257

<https://www.phoenixcontact.com/us/products/1014257>

| | |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Temperature resistance

| | |
|------------------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |
| Rating 150 °C (180 °C) | Test passed |

Wipe resistance of inscriptions

| | |
|---|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |

Immersion in chemicals, oil & fuel

| | |
|---|--------------------------|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |
| Saltwater (saturated 350 g/l) [CAS No. -] | Test passed |
| Diesel [CAS No. 68476-34-6] | Test passed |
| IRM 901 | Test passed |
| IRM 902 | Test passed |
| IRM 903 | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |
| Test duration | 96 h |

Standards and regulations

PML-T105 (26X280)R CUS - Pipeline marker



1014257

<https://www.phoenixcontact.com/us/products/1014257>

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

PML-T105 (26X280)R CUS - Pipeline marker



1014257

<https://www.phoenixcontact.com/us/products/1014257>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-15.0 | 40200202 |
| ECLASS-13.0 | 40200202 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001777 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 55121700 |
|-------------|----------|

PML-T105 (26X280)R CUS - Pipeline marker



1014257

<https://www.phoenixcontact.com/us/products/1014257>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com