

PML-GHS104 (25X25) - Hazardous substances label



1014276

<https://www.phoenixcontact.com/us/products/1014276>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Hazardous substances label, Sheet, labeled: Pressurized gases, mounting type: adhesive, diameter: 0 mm, Number of individual labels: 4

Your advantages

- High adhesive strength
- High temperature resistance
- Stick-on hazardous substances labels, preprinted with symbol
- The markers conform to the GHS international standard
- Suitable for indoor and outdoor use

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1014276 |
| Packing unit | 5 pc |
| Minimum order quantity | 1 pc |
| Product key | BG2624 |
| GTIN | 4046356786935 |
| Weight per piece (including packing) | 5.89 g |
| Weight per piece (excluding packing) | 5.89 g |
| Country of origin | DE |

PML-GHS104 (25X25) - Hazardous substances label



1014276

<https://www.phoenixcontact.com/us/products/1014276>

Technical data

Product properties

| | |
|---------------------|--|
| Product type | Plant marker |
| Area of application | Hazardous substance labels |
| | Hazardous substance labeling according to CLP/GHS regulation |
| Type | Diamond |

Marking

| | |
|-----------------------------|-------------------|
| Number of individual labels | 4 |
| Printing | Pressurized gases |

Dimensions

| | |
|--------|-------|
| Width | 25 mm |
| Height | 25 mm |
| Length | 25 mm |

Material specifications

| | |
|------------|---------------|
| Color | red/white |
| Material | Polyester |
| Components | Silicone-free |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 150 °C |
|---------------------------------|-------------------|

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

PML-GHS104 (25X25) - Hazardous substances label



1014276

<https://www.phoenixcontact.com/us/products/1014276>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com