PML-GHS107 (25X25) - Hazardous substances label

1014282

https://www.phoenixcontact.com/us/products/1014282

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Hazardous substances label, Sheet, labeled: Irritant, mounting type: adhesive, diameter: 0 mm, Number of individual labels: 9, text field height: 25 mm, text field width: 25 mm

Your advantages

- High adhesive strength
- High temperature resistance
- Stick-on hazardous substances labels, preprinted with symbol
- The markers conform to the GHS international standard
- Suitable for indoor and outdoor use

Commercial data

Item number	1014282
Packing unit	5 pc
Minimum order quantity	1 pc
Product key	BG2624
GTIN	4046356786997
Weight per piece (including packing)	5.91 g
Weight per piece (excluding packing)	5.91 g
Country of origin	DE

Technical data

Product properties

Product type	Plant marker
Area of application	Hazardous substance labels
	Hazardous substance labeling according to CLP/GHS regulation
Type	Diamond

Marking

Number of individual labels	9
Printing	Irritant

Dimensions

Width	25 mm
Height	25 mm
Length	25 mm

Text field

Text field width	25 mm
Text field height	25 mm

Material specifications

Color	red/white
Material	Polyester
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type	adhesive

Classifications

ECLASS

ECLASS-13.0	40200202

ETIM

ETIM 9.0	EC001777

UNSPSC

UNSPSC 21.0	55121700

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com