

US-PML-GHS100 (13X13) - Hazardous substances label



1014287

<https://www.phoenixcontact.com/us/products/1014287>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Hazardous substances label, Card, Mixed color, unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD: Diamond, mounting type: adhesive, Number of individual labels: 50, text field height: 13 mm, text field width: 13 mm



Your advantages

- Stick-on hazardous substances labels, color preprinted, without symbol
- Suitable for indoor and outdoor use
- The markers conform to the GHS international standard
- High adhesive strength
- High temperature resistance

Commercial data

Item number	1014287
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG09
Product key	BG2619
GTIN	4046356786614
Weight per piece (including packing)	6.43 g
Weight per piece (excluding packing)	6.43 g
Customs tariff number	39199080
Country of origin	DE

US-PML-GHS100 (13X13) - Hazardous substances label



1014287

<https://www.phoenixcontact.com/us/products/1014287>

Technical data

Product properties

Product type	Plant marker
Area of application	Hazardous substance labels
	Hazardous substance labeling according to CLP/GHS regulation
Type	Diamond

Marking

Number of individual labels	50
Printing	Diamond
Identification technology	Thermal transfer

Dimensions

Width	13.00 mm
Height	13.00 mm
Depth	0.08 mm

Text field

Text field width	13 mm
Text field height	13 mm

Material specifications

Color	multicolored (RAL -)
	red (RAL 3001)
	white (RAL 9010)
Base element material	Polyester
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

US-PML-GHS100 (13X13) - Hazardous substances label



1014287

<https://www.phoenixcontact.com/us/products/1014287>

Mounting

Mounting type
adhesive

US-PML-GHS100 (13X13) - Hazardous substances label



1014287

<https://www.phoenixcontact.com/us/products/1014287>

Classifications

ECLASS

ECLASS-15.0	40200202
ECLASS-13.0	40200202

ETIM

ETIM 10.0	EC001777
-----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

US-PML-GHS100 (13X13) - Hazardous substances label



1014287

<https://www.phoenixcontact.com/us/products/1014287>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com