

PMM (EX20)R YE - Magnetic label

1014305

<https://www.phoenixcontact.com/us/products/1014305>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Magnetic label, Roll, yellow (RAL 1018), unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: magnetic adhesion, Number of individual labels: 1, roll length: 15 m, text field height: 20 mm, text field width: 15000 mm

Your advantages

- The magnetic labels supplied in rolls represent an individual and flexible marking solution, e.g., for warehouse marking
- High adhesive strength
- The flexible magnetic tape will also adhere to round objects with a radius from 12 mm
- Magnetic tape coated with polyester foil
- Magnetic labels, unprinted

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1014305 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG21 |
| Product key | BG2611 |
| GTIN | 4046356786096 |
| Weight per piece (including packing) | 626.5 g |
| Weight per piece (excluding packing) | 626.5 g |
| Customs tariff number | 39207380 |
| Country of origin | BE |

PMM (EX20)R YE - Magnetic label



1014305

<https://www.phoenixcontact.com/us/products/1014305>

Technical data

Product properties

| | |
|---------------------|-----------------------|
| Product type | Plant marker |
| Area of application | Magnetic labels |
| | Warehousing/logistics |
| Product property | magnetic |

Marking

| | |
|-------------------------------------|----------------|
| Number of individual labels | 1 |
| Number of individual labels per row | 1 |
| Identification technology | Thermotransfer |

Dimensions

| | |
|----------------|----------|
| Length of roll | 15.00 m |
| Height | 20.00 mm |
| Depth | 0.60 mm |

Text field

| | |
|-------------------|----------|
| Text field width | 15000 mm |
| Text field height | 20 mm |

Material specifications

| | |
|-----------------------|-------------------|
| Color | yellow (RAL 1018) |
| Material | Magnetic tape |
| Coating | Polyester foil |
| Base element material | Magnetic tape |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -30 °C ... 55 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |

Wipe resistance of inscriptions

| | |
|--------------------------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |

PMM (EX20)R YE - Magnetic label



1014305

<https://www.phoenixcontact.com/us/products/1014305>

| | |
|---|-------------|
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
|---|-------------|

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|-------------------|
| Mounting type | magnetic adhesion |
|---------------|-------------------|

PMM (EX20)R YE - Magnetic label



1014305

<https://www.phoenixcontact.com/us/products/1014305>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281104 |
| ECLASS-15.0 | 27281104 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

PMM (EX20)R YE - Magnetic label



1014305

<https://www.phoenixcontact.com/us/products/1014305>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com