

# SAC-4P-M 8MS/0,45-PUR 0,34 - Sensor/actuator cable



1016894

<https://www.phoenixcontact.com/us/products/1016894>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, Plug straight M8, coding: A, on free cable end, cable length: 0.45 m

## Commercial data

Item number	1016894
Packing unit	1 pc
Minimum order quantity	100 pc
Product key	AF1BCA
GTIN	4055626499406
Weight per piece (including packing)	18.56 g
Weight per piece (excluding packing)	18.56 g
Country of origin	DE

# SAC-4P-M 8MS/0,45-PUR 0,34 - Sensor/actuator cable

1016894

<https://www.phoenixcontact.com/us/products/1016894>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	4

### Electrical properties

Nominal voltage $U_N$	48 V AC
	60 V DC

### Connector

#### Connection 1

Type	Plug straight M8
Coding type	A

#### Connection 2


Type	free cable end
------	----------------

### Cable/line

Cable length	0.45 m
--------------	--------

#### PUR halogen-free black [PUR]

##### Dimensional drawing



Cable weight	30 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Number of positions	4
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross-section	4x 0.34 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.27 mm ±0.02 mm
External cable diameter	4.20 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP

# SAC-4P-M 8MS/0,45-PUR 0,34 - Sensor/actuator cable



1016894

<https://www.phoenixcontact.com/us/products/1016894>

Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.21 mm
Thickness, outer sheath	approx. 0.50 mm
Overall twist	4 wires, twisted
Max. conductor resistance	≤ 58 Ω/km
Insulation resistance	≥ 1 GΩ*km
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	21 mm
Smallest bending radius, movable installation	42 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 42 mm, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup>
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥5000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815 in accordance with DIN EN 50267-2-1
Flame resistance	in accordance with UL 758/1581 FT2 DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents hydrolysis and microbe resistant partly UV-resistant (in accordance with DIN EN ISO 4892-2-A) Low adhesion abrasion-resistant
Special properties	Flexible cable conduit capable Silicone-free Free of substances which would hinder coating with paint or varnish flexible
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -25 °C ... 80 °C (Cable, flexible installation)

# SAC-4P-M 8MS/0,45-PUR 0,34 - Sensor/actuator cable



1016894

<https://www.phoenixcontact.com/us/products/1016894>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

### UNSPSC

UNSPSC 21.0	31251501
-------------	----------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)