

AGK PT 4X6/M10 - Pick-off terminal block



1017448

<https://www.phoenixcontact.com/us/products/1017448>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Terminal point designation,
alphabetical

Pick-off terminal block, nom. voltage: 1000 V, nominal current: 41 A, number of connections: 5, connection method: Push-in connection, Rated cross section: 6 mm², 1 level, cross section: 0.5 mm² - 10 mm², Bolt connection, Line contact, mounting type: on base element, color: gray

Your advantages

- The fully insulated, optionally used pick-off terminal block enables voltage pick-off
- Large-surface marking

Commercial data

Item number	1017448
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2ZWX
GTIN	4055626500638
Weight per piece (including packing)	41.13 g
Weight per piece (excluding packing)	37.7 g
Customs tariff number	85369010
Country of origin	CN

AGK PT 4X6/M10 - Pick-off terminal block



1017448

<https://www.phoenixcontact.com/us/products/1017448>

Technical data

Notes

General

Note	For power distribution applications, IEC 60364-4-43:2008; modified + corrigendum Okt. 2008 (DIN VDE 0100-430:2010-10) section 433.2 ff must be observed!
------	--

Product properties

Product type	Pick-off terminal
Product family	PT
Number of connections	5
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
----------------------	-----

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.31 W

Connection data

Number of connections per level	5
Nominal cross section	6 mm ²
Rated cross section AWG	10

1 level

Connection method	Push-in connection
Stripping length	10 mm ... 12 mm
Internal cylindrical gage	A5
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	0.5 mm ² ... 10 mm ²
Cross section AWG	20 ... 8 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 6 mm ²
Conductor cross-section, flexible [AWG]	20 ... 10 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 6 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 6 mm ²
Conductor cross-section flexible (2 conductors with the same cross-section, with TWIN ferrule and plastic sleeve)	0.5 mm ² ... 1.5 mm ²
Nominal cross section	6 mm ²
Nominal current	41 A
Maximum load current	57 A
Maximum total current	109 A (Bolt connection)
Nominal voltage	1000 V (when using HV M 10/2 or HV M 10/1 and appropriate)

AGK PT 4X6/M10 - Pick-off terminal block



1017448

<https://www.phoenixcontact.com/us/products/1017448>

	partition plate)
--	------------------

Line contact

Connection method	Bolt connection
Screw thread	M10
Note	Connection bolts
Tightening torque	10 ... 20 Nm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section flexible	6 mm ² ... 120 mm ²
Conductor cross-section, flexible [AWG]	10 ... 250 kcmil (converted acc. to IEC)

Cable lug connection

Cross section range AWG	(converted acc. to IEC)
Hole diameter	10.4 mm
Width	32 mm
Bolt diameter	10 mm
Screw thread	M10

Dimensions

Width	31 mm
Height	57.4 mm
Depth	32.3 mm
Hole diameter	10.4 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Electrical tests

Surge voltage test

Test voltage setpoint	9.8 kV
-----------------------	--------

AGK PT 4X6/M10 - Pick-off terminal block



1017448

<https://www.phoenixcontact.com/us/products/1017448>

Result	Test passed
--------	-------------

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 6 mm ²	0.72 kA
Short-time withstand current 10 mm ²	1.2 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	2.2 kV
Result	Test passed

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

DIN rail/fixing support	NS 35
Test force setpoint	5 N
Result	Test passed

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135
Conductor cross-section/weight	0.5 mm ² / 0.3 kg
	6 mm ² / 1.4 kg
	10 mm ² / 2 kg
Result	Test passed

Environmental and real-life conditions

Aging

Temperature cycles	192
Result	Test passed

Needle-flame test

Time of exposure	30 s
Result	Test passed

Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Spectrum	Long life test category 2, bogie-mounted

AGK PT 4X6/M10 - Pick-off terminal block



1017448

<https://www.phoenixcontact.com/us/products/1017448>

Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$
ASD level	6.12 (m/s ²) ² /Hz
Acceleration	3.12g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Pulse shape	Half-sine
Acceleration	30g
Shock duration	18 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
	IEC 60947-7-1

Mounting

Mounting type	on base element
---------------	-----------------

AGK PT 4X6/M10 - Pick-off terminal block



1017448

<https://www.phoenixcontact.com/us/products/1017448>

Drawings

Circuit diagram



AGK PT 4X6/M10 - Pick-off terminal block



1017448

<https://www.phoenixcontact.com/us/products/1017448>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1017448>

DNV

Approval ID: TAE000037B



CSA

Approval ID: 158887

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
C				
Output	1000 V	50 A	20 - 8	-
Input	1000 V	100 A	-	-



EAC

Approval ID: RU C-DE.BL08.B.00644



cULus Recognized

Approval ID: E60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
F				
Output	1000 V	50 A	20 - 8	-
Input	1000 V	100 A	-	-
E				
Output	1000 V	50 A	20 - 8	-
Input	1000 V	100 A	-	-

AGK PT 4X6/M10 - Pick-off terminal block



1017448

<https://www.phoenixcontact.com/us/products/1017448>

Classifications

ECLASS

ECLASS-13.0	27250308
ECLASS-15.0	27250308

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

AGK PT 4X6/M10 - Pick-off terminal block



1017448

<https://www.phoenixcontact.com/us/products/1017448>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.523 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com