

# FOC-17P12-17P12-GL02/200 - Fiber optic cable



1018562

<https://www.phoenixcontact.com/us/products/1018562>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fiber optic cable, degree of protection: IP65/IP67, cable length: 200 m



## Your advantages

- The connector is small and compact, and it has a maximum outer diameter of 21 mm, which enables high-density installation
- Prefabricated FO connection assembly, no fusion splicing required on site, plug and play
- IP67 degree of protection, stainless steel housing, ambient temperature -40 °C ... +85 °C, suitable for industrial applications and harsh environments
- Armored fiber FO cable for indoor and outdoor applications, low smoke and free of halogen, standard length can be ordered from 10 m ... 200 m, customized length on request
- The connector has integrated protective cover, so that it can be used on site conveniently

## Commercial data

Item number	1018562
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB15
Product key	ABNHBA
GTIN	4055626503479
Weight per piece (including packing)	10,972 g
Weight per piece (excluding packing)	10,972 g
Customs tariff number	85447000
Country of origin	CN

# FOC-17P12-17P12-GL02/200 - Fiber optic cable



1018562

<https://www.phoenixcontact.com/us/products/1018562>

## Technical data

### Product properties

Product type	Data cable preassembled
Number of positions	12

### Electrical properties

Transmission medium	Multi-mode fiberglass
---------------------	-----------------------

### Mechanical properties

Tensile strength short-term/long-term	1500 N / 800N
---------------------------------------	---------------

### Material specifications

Flammability rating according to UL 94	V0
Ferrule material	MPO
Outer sheath, material	LSZH

### Connector

#### Connection 1

Locking type	17# thread type
Handle color	black
Material	Stainless steel
Degree of protection	IP67 (IEC 60529)

#### Connection 2

Locking type	Screw locking mechanism
Material	Stainless steelStainless steel
Degree of protection	IP67 (IEC 60529)

### Cable/line

Cable length	200 m
Cable weight	40.00 kg/km
Cable type	Multimode fiberglass
Cable type	Non-metal armored fiber optic cable for indoor/outdoor applications
External cable diameter	7.5 mm
Outer sheath, material	LSZH
External sheath, color	black
Wire diameter incl. insulation	250 µm
Smallest bending radius, fixed installation	≥ 80 mm
Tensile strength short-term/long-term	1500 N / 800N
Lateral pressure, long-term	300.00 N/cm
Halogen-free	according to IEC 60754-1

FO cable

# FOC-17P12-17P12-GL02/200 - Fiber optic cable



1018562

<https://www.phoenixcontact.com/us/products/1018562>

Number of fibers	12
Fiber	62.5/125 µm OM1
Fiber type	Multimode fiberglass 62.5/125 µm
Attenuation	≤ 1.2 dB (1300 nm)
Transmission medium	Multi-mode fiberglass

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 85 °C
Shock	50g, in accordance with IEC 61300-2-9

# FOC-17P12-17P12-GL02/200 - Fiber optic cable



1018562

<https://www.phoenixcontact.com/us/products/1018562>

## Classifications

### ECLASS

ECLASS-13.0	27061003
ECLASS-15.0	27061003

### ETIM

ETIM 10.0	EC002700
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# FOC-17P12-17P12-GL02/200 - Fiber optic cable



1018562

<https://www.phoenixcontact.com/us/products/1018562>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)