

FTP-3F/14 - Test plug

1029269

<https://www.phoenixcontact.com/us/products/1029269>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug, nom. voltage: 400 V, nominal current: 20 A, number of positions: 14, connection method: Cable lug connection, Rated cross section: 2.5 mm², color: gray

Commercial data

Item number	1029269
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE06
Product key	BE6114
GTIN	4055626531250
Weight per piece (including packing)	719.7 g
Weight per piece (excluding packing)	719 g
Customs tariff number	85366990
Country of origin	PL

FTP-3F/14 - Test plug



1029269

<https://www.phoenixcontact.com/us/products/1029269>

Technical data

Product properties

Product type	Test plug terminal block
Product family	FAME 3 RACK
Number of positions	14

Electrical properties

Maximum power dissipation for nominal condition	1.02 W
---	--------

Connection data

Nominal cross section	4 mm ²
Test socket torque	0.5
Connection method	Cable lug connection
Conductor cross-section flexible	0.5 mm ² ... 2.5 mm ²
Conductor cross-section, flexible [AWG]	20 ... 14 (converted acc. to IEC)
Nominal cross section	2.5 mm ²
Nominal current	20 A
Maximum load current	20 A
Nominal voltage	400 V

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

FTP-3F/14 - Test plug


1029269

<https://www.phoenixcontact.com/us/products/1029269>



Drawings

Circuit diagram



FTP-3F/14 - Test plug





1029269

<https://www.phoenixcontact.com/us/products/1029269>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1029269>

 **CSA**
Approval ID: 13631

 **cUL Recognized**
Approval ID: FILE E 60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	300 V	30 A	-	-
C				
	300 V	30 A	-	-
F				
	400 V	30 A	-	-

 **UL Recognized**
Approval ID: FILE E 60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	300 V	30 A	-	-
C				
	300 V	30 A	-	-
F				
	400 V	30 A	-	-

FTP-3F/14 - Test plug



1029269

<https://www.phoenixcontact.com/us/products/1029269>

Classifications

ECLASS

ECLASS-15.0	27250304
ECLASS-13.0	27250304

ETIM

ETIM 10.0	EC002555
-----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

FTP-3F/14 - Test plug



1029269

<https://www.phoenixcontact.com/us/products/1029269>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	072d51b1-5683-4b01-a937-84bd924050a7

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com