# CC1,5-TS-2,10F K/L AU - Crimp contact

1029396

https://www.phoenixcontact.com/us/products/1029396

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, Socket, turned, contact diameter: 1.5 mm, connection cross section: 1.5 mm$^2$ ... 1.5 mm$^2$, AWG 14...14 , contact material: CuZn

## Commercial data

| | |
|---|---|
| Item number | 1029396 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BF34 |
| Product key | AF2CJB |
| GTIN | 4055626531403 |
| Weight per piece (including packing) | 0.427 g |
| Weight per piece (excluding packing) | 0.427 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

## Technical data

### Mounting

| | |
|---|---|
| Mounting type | Snap in |

### Product properties

| | |
|---|---|
| Product type | Crimp contact |
| Contact material type | turned |

### Connection data

Connection technology

| | |
|---|---|
| Contact connection type | Socket |
| Connection method | Crimp connection |


Conductor connection

| | |
|---|---|
| Connection cross section (flexible) | 1.5 mm² ... 1.5 mm² |
| Connection cross section AWG (flexible) | 14 ... 14 |

### Material specifications

| | |
|---|---|
| Material Contact | CuZn |
| Material Contact surface | Ni/Au |

### Dimensions

| | |
|---|---|
| Dimensional drawing |  |
| Diameter (Contact diameter) | 1.5 mm |

### Mechanical properties

Mechanical data

| | |
|---|---|
| Insertion/withdrawal cycles | ≥ 100 |


### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 85 °C |

## Drawings

Dimensional drawing




Crimp contact, diameter: 1.5 mm

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440204 |
| ECLASS-15.0 | 27440204 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000796 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.412 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com