

CUC-PPC-C2ZNI-SX/24FKP5:FCWO - Power connector



1032275

<https://www.phoenixcontact.com/us/products/1032275>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power connector, degree of protection: IP65/IP67, number of positions: 5, material: Die-cast zinc, cable outlet: straight, Universal

Your advantages

- Fixed coding
- Increased temperature range
- Lockable
- One-part housing

Commercial data

Item number	1032275
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABNOHA
GTIN	4055626536385
Weight per piece (including packing)	116.451 g
Weight per piece (excluding packing)	116.451 g
Country of origin	PL

CUC-PPC-C2ZNI-SX/24FKP5:FCWO - Power connector



1032275

<https://www.phoenixcontact.com/us/products/1032275>

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 11 Connectors for 24 Volt Power Supply Cabling and Chapter 13 Application specific Cabling and Interconnection Technology (AIDA)
---------	---

Product properties

Product type	Data cable preassembled
Type	MSTB
Sensor type	Universal
Number of positions	5
Connection profile	MSTB
Cable outlet	straight

Insulation characteristics

Degree of pollution	3
---------------------	---

Electrical properties

Nominal voltage U_N	24 V
Nominal current I_N	16 A

Material specifications

Material	Metal
Flammability rating according to UL 94	V0
Seal material	NBR
Housing material	Die-cast zinc
Housing surface material	nickel-plated
Cable seal material	TPE
Contact material	Copper alloy
Contact surface material	Gold over nickel
Contact carrier material	PA

Dimensions

Width	31 mm
Height	36 mm
Length	67 mm

Cable/line

External cable diameter	9 mm ... 13 mm
-------------------------	----------------

CUC-PPC-C2ZNI-SX/24FKP5:FCWO - Power connector




1032275

<https://www.phoenixcontact.com/us/products/1032275>

Drawings

Schematic diagram



Pin assignment PROFINET push-pull, power connector, 24 V, flexible coding

CUC-PPC-C2ZNI-SX/24FKP5:FCWO - Power connector




1032275

<https://www.phoenixcontact.com/us/products/1032275>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1032275>

 cULus Recognized Approval ID: E118976-20080903				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	24 V	16 A	- 14	-

CUC-PPC-C2ZNI-SX/24FKP5:FCWO - Power connector



1032275

<https://www.phoenixcontact.com/us/products/1032275>

Classifications

ECLASS

ECLASS-13.0	27440114
ECLASS-15.0	27440114

ETIM

ETIM 10.0	EC002636
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-PPC-C2ZNI-SX/24FKP5:FCWO - Power connector



1032275

<https://www.phoenixcontact.com/us/products/1032275>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com