

FOC-SHRINKSPLICE-PROTECT - Shrink splice protection



1019676

<https://www.phoenixcontact.com/us/products/1019676>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink splice protection, design: Straight, degree of protection: IP20, cable outlet: above and below, color: transparent

Product description

Shrink splice protection

Your advantages

- No attenuating effects on the fusion splice
- Mechanical protection for fusion splices
- Bellcore GR-1380-CORE (Telcordia)
- BT (British Telecom)

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1019676 |
| Packing unit | 12 pc |
| Minimum order quantity | 12 pc |
| Sales key | AB15 |
| Product key | ABNGAZ |
| GTIN | 4055626701196 |
| Weight per piece (including packing) | 0.263 g |
| Weight per piece (excluding packing) | 0.07 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

FOC-SHRINKSPLICE-PROTECT - Shrink splice protection



1019676

<https://www.phoenixcontact.com/us/products/1019676>

Technical data

Notes

| | |
|--------------------|---|
| Order information: | Splice protection for FDX 20 splice boxes |
| Assembly note | 120°C for 30 seconds (type-dependent) |

Product properties

| | |
|--------------|-------------------------|
| Product type | Network distributor box |
| Housing type | Fiber optic |
| Cable outlet | above and below |

Dimensions

| | |
|--------|--------|
| Height | 1.3 mm |
| Depth | 0.5 mm |
| Length | 30 mm |

Material specifications

| | |
|----------|------------------------------|
| Color | transparent |
| Material | Ethylene-vinyl acetate (EVA) |

Cable/line

| | |
|-------------------------|-----------------------------------|
| Cable type | Fiberglass |
| External cable diameter | 250 µm (Includes primary coating) |

FO cable

| | |
|---------------------|----|
| Transmission medium | FO |
|---------------------|----|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|--|
| Degree of protection | IP20 |
| | IP20 |
| Ambient temperature (operation) | -40 °C ... 70 °C (according to DIN EN 61300-2) |

Mounting

| | |
|---------------|--|
| Mounting type | Shrink splice protection |
| Assembly note | Shrink splice protection clicks into the splice holder |

FOC-SHRINKSPLICE-PROTECT - Shrink splice protection



1019676

<https://www.phoenixcontact.com/us/products/1019676>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19170192 |
| ECLASS-15.0 | 19170192 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003626 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121650 |
|-------------|----------|

FOC-SHRINKSPLICE-PROTECT - Shrink splice protection



1019676

<https://www.phoenixcontact.com/us/products/1019676>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com