

# SAC-3P-0,6-PUR/M 8FS 0,34 NC - Sensor/actuator cable



1034020

<https://www.phoenixcontact.com/us/products/1034020>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket straight M8, cable length: 0.6 m, Shield not connected to knurl

## Commercial data

Item number	1034020
Packing unit	1 pc
Minimum order quantity	100 pc
Product key	AF1BBA
GTIN	4055626540764
Weight per piece (including packing)	20.4 g
Weight per piece (excluding packing)	20.2 g
Country of origin	PL

# SAC-3P-0,6-PUR/M 8FS 0,34 NC - Sensor/actuator cable

1034020

<https://www.phoenixcontact.com/us/products/1034020>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	3

### Connector

#### Connection 1

Type	free cable end
------	----------------


#### Connection 2

Type	Socket straight M8
Number of positions	3

### Cable/line

Cable length	0.6 m
--------------	-------

#### PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	26 kg/km
UL AWM Style	20549
Number of positions	3
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross-section	3x 0.34 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.27 mm ±0.02 mm (Signal line)
External cable diameter	4.40 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.21 mm (Core insulation)
Thickness, outer sheath	approx. 0.80 mm
Overall twist	3 wires, twisted

# SAC-3P-0,6-PUR/M 8FS 0,34 NC - Sensor/actuator cable



1034020

<https://www.phoenixcontact.com/us/products/1034020>

Max. conductor resistance	max. 58 Ω/km (at 20 °C)
Insulation resistance	≥ 100 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	22 mm
Smallest bending radius, movable installation	44 mm
Dynamic load capacity (bending)	Max. bending cycles: 4000000, Bending radius: 44 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup>
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with DIN UL-Style 20549
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents
	hydrolysis and microbe resistant
	partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Flexible cable conduit capable
	Silicone-free
	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-25 °C ... 80 °C (Cable, flexible installation)

# SAC-3P-0,6-PUR/M 8FS 0,34 NC - Sensor/actuator cable



1034020

<https://www.phoenixcontact.com/us/products/1034020>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-3P-0,6-PUR/M 8FS 0,34 NC - Sensor/actuator cable



1034020

<https://www.phoenixcontact.com/us/products/1034020>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)