

UT 4-HESI (5X20)-EX - Fuse modular terminal block



1021498

<https://www.phoenixcontact.com/us/products/1021498>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse modular terminal block, fuse type: Glass / ceramics / ..., fuse type: G / 5 x 20, connection method: Screw connection, Rated cross section: 4 mm², cross section: 0.14 mm²- 6 mm², mounting type: NS 35/7,5, NS 35/15, color: black

Your advantages

- Globally recognized: Internationally proven screw connection
- Maintenance-free and vibration-resistant thanks to the patented Reakdyn principle
- Easy integration and replacement of fuses with the lever element
- Easy checking of the fuses with integrated test pick-offs
- Long-term stable connections with the use of high-quality materials
- Long-term stable connections with the use of high-quality materials
- Maximum efficiency in the smallest space - thanks to integrated level bridging, the connections are connected across levels

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1021498 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE01 |
| Product key | BE1134 |
| GTIN | 4055626514253 |
| Weight per piece (including packing) | 17.544 g |
| Weight per piece (excluding packing) | 17.544 g |
| Customs tariff number | 85369095 |
| Country of origin | PL |

UT 4-HESI (5X20)-EX - Fuse modular terminal block



1021498

<https://www.phoenixcontact.com/us/products/1021498>

Technical data

Notes

| | |
|--------------------|------------------------------------|
| Order information: | Fuse-link not supplied as standard |
|--------------------|------------------------------------|

Product properties

| | |
|-----------------------|---------------------|
| Product type | Fuse terminal block |
| Product family | UT |
| Area of application | Railway industry |
| | Machine building |
| | Plant engineering |
| Number of connections | 2 |
| Number of rows | 1 |
| Potentials | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--|
| Fuse type | Glass / ceramics / ... |
| Rated surge voltage | 6 kV |
| Maximum power dissipation for nominal condition | 1.02 W |
| Fuse | G / 5 x 20 |
| Maximum power dissipation | max. 1.6 W (with single arrangement of the fuse terminal block in the event of overload) |
| | max. 1.6 W (With interconnected arrangement of several fuse terminal blocks in the event of overload) |
| | max. 4 W (with single arrangement of the fuse terminal block in the event of a short-circuit) |
| | max. 2.5 W (With interconnected arrangement of several fuse terminal blocks in the event of a short-circuit) |

Connection data

| | |
|---|--|
| Number of connections per level | 2 |
| Nominal cross section | 4 mm ² |
| Connection method | Screw connection |
| Screw thread | M3 |
| Tightening torque | 0.6 ... 0.8 Nm |
| Stripping length | 9 mm |
| Internal cylindrical gage | A4 |
| Conductor cross-section rigid | 0.14 mm ² ... 6 mm ² |
| Cross section AWG | 26 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.14 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] | 26 ... 10 (converted acc. to IEC) |

UT 4-HESI (5X20)-EX - Fuse modular terminal block



1021498

<https://www.phoenixcontact.com/us/products/1021498>

| | |
|---|--|
| Conductor cross-section flexible ultrasound-compressed | 0.34 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] ultrasound-compressed | 22 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.14 mm ² ... 4 mm ² |
| 2 conductors with same cross section, rigid | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with same cross section, flexible | 0.14 mm ² ... 1.5 mm ² |
| Nominal cross section | 4 mm ² |

Ex data

Rated data (ATEX/IECEx)

| | |
|-----------------------------|-----------------------|
| Identification | Ⓜ II 3 G Ex ec IIC Gc |
| Operating temperature range | -60 °C ... 130 °C |
| Ex-certified accessories | 1205053 SZS 0,6X3,5 |
| | 3022276 CLIPFIX 35-5 |
| | 3022218 CLIPFIX 35 |
| Rated insulation voltage | 250 V |
| output | (Permanent) |

Ex level General

| | |
|----------------------|----------------------------|
| Rated voltage | 275 V |
| Rated current | 6.3 A (4 mm ²) |
| Maximum load current | 6.3 A (6 mm ²) |
| Contact resistance | 5 mΩ |

Ex connection data General

| | |
|--|--|
| Torque range | 0.6 Nm ... 0.8 Nm |
| Nominal cross section | 4 mm ² |
| Rated cross section AWG | 12 |
| Connection capacity rigid | 0.14 mm ² ... 6 mm ² |
| Connection capacity AWG | 26 ... 10 |
| Connection capacity flexible | 0.14 mm ² ... 6 mm ² |
| Connection capacity AWG | 26 ... 10 |
| 2 conductors with same cross section, solid | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with the same cross-section AWG rigid | 26 ... 16 |
| 2 conductors with same cross section, stranded | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with the same cross-section AWG flexible | 26 ... 16 |
| Conductor cross-section flexible, with ferrule without plastic sleeve min. | 0.14 mm ² |
| Conductor cross-section flexible, with ferrule without plastic sleeve max. | 4 mm ² |
| Single conductor/terminal point, flexible, with ferrule, without plastic sleeve, AWG | 26 ... 12 |

Dimensions

| | |
|-------|--------|
| Width | 6.2 mm |
|-------|--------|

UT 4-HESI (5X20)-EX - Fuse modular terminal block



1021498

<https://www.phoenixcontact.com/us/products/1021498>

| | |
|--------------------|---------|
| Height | 57.8 mm |
| Depth on NS 35/7,5 | 75.6 mm |
| Depth on NS 35/15 | 83.1 mm |

Material specifications

| | |
|--|------------------|
| Color | black (RAL 9005) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |

UT 4-HESI (5X20)-EX - Fuse modular terminal block



1021498

<https://www.phoenixcontact.com/us/products/1021498>

Drawings

Application drawing



Fuse terminal blocks in interconnected arrangement,
block consisting of 5 fuse terminal blocks

UT 4-HESI (5X20)-EX - Fuse modular terminal block



1021498

<https://www.phoenixcontact.com/us/products/1021498>

Application drawing



Fuse terminal block in single arrangement,
block consisting of one fuse terminal block and 4 feed-through terminal blocks

UT 4-HESI (5X20)-EX - Fuse modular terminal block



1021498

<https://www.phoenixcontact.com/us/products/1021498>

Circuit diagram



UT 4-HESI (5X20)-EX - Fuse modular terminal block





1021498


<https://www.phoenixcontact.com/us/products/1021498>

Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1021498>


|  cUL Recognized Approval ID: E192998 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 500 V | 10 A | 26 - 10 | - |

|  IECEx Approval ID: IECExKIWA14.0014U | | | | |
|--|--|--|--|--|
|--|--|--|--|--|

|  UL Recognized Approval ID: E192998 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 500 V | 10 A | 26 - 10 | - |

|  ATEX Approval ID: KIWA14ATEX0025U | | | | |
|---|--|--|--|--|
|---|--|--|--|--|

|  UKCA-EX Approval ID: CSAE 21UKEX3606U | | | | |
|---|--|--|--|--|
|---|--|--|--|--|

|  EAC Ex Approval ID: KZ 7500525010101950 | | | | |
|---|--|--|--|--|
|---|--|--|--|--|

UT 4-HESI (5X20)-EX - Fuse modular terminal block



1021498

<https://www.phoenixcontact.com/us/products/1021498>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250113 |
| ECLASS-15.0 | 27250113 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000899 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

UT 4-HESI (5X20)-EX - Fuse modular terminal block



1021498

<https://www.phoenixcontact.com/us/products/1021498>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | b85c1bff-8702-445b-bf6a-d8f32d87899f |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.165 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com