

# NBC-M12MSD/2,37-93B CV - Network cable



1036682

<https://www.phoenixcontact.com/us/products/1036682>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, PROFINET CAT5, 4-position, shielded, Plug straight M12, coding: D / IP67, on free cable end, cable length: 2.37 m, Pre-construction stage

## Commercial data

Item number	1036682
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CMI
GTIN	4055626569338
Weight per piece (including packing)	167.3 g
Weight per piece (excluding packing)	167 g
Country of origin	PL

1036682

<https://www.phoenixcontact.com/us/products/1036682>

## Technical data

### Product properties

Product type	Data cable preassembled
Sensor type	PROFINET
Number of positions	4

### Interfaces

Signal type/category	PROFINET CAT5 (IEC 11801)
----------------------	---------------------------

### Material specifications

Outer sheath, material	PVC
------------------------	-----

### Connector

#### Connection 1

Type	Plug straight M12 / IP67
Coding type	D
Degree of protection	IP67

#### Connection 2

Type	free cable end
------	----------------

### Cable/line

Cable length	2.37 m
Signal type/category	PROFINET CAT5 (IEC 11801)
Outer sheath, material	PVC
External sheath, color	green RAL 6018
Material, inner sheath	PVC

# NBC-M12MSD/2,37-93B CV - Network cable



1036682

<https://www.phoenixcontact.com/us/products/1036682>

## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# NBC-M12MSD/2,37-93B CV - Network cable



1036682

<https://www.phoenixcontact.com/us/products/1036682>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)