

FL SFP LX10-B - Media module



1025401

<https://www.phoenixcontact.com/us/products/1025401>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Gigabit SFP module for transmission up to 10 km with a wavelength of 1310 nm.



Product description

DDI, Digital Diagnostic Monitoring Interface

Your advantages

- MSA compliant

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1025401 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN22 |
| Product key | DNN613 |
| GTIN | 4055626517148 |
| Weight per piece (including packing) | 29.8 g |
| Weight per piece (excluding packing) | 29.8 g |
| Customs tariff number | 85176200 |
| Country of origin | TW |

FL SFP LX10-B - Media module



1025401

<https://www.phoenixcontact.com/us/products/1025401>

Technical data

Dimensions

| | |
|--------|---------|
| Width | 13.7 mm |
| Height | 8.95 mm |
| Length | 56.5 mm |

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Mounting

| | |
|---------------|-----------------------------|
| Mounting type | Plug-in mounting (SFP port) |
|---------------|-----------------------------|

Interfaces

Ethernet FO

| | |
|------------------------------|-------------------------------------|
| Connection method | LC |
| Transmission speed | 1 Gbps |
| Transmit capacity, minimum | -9.5 dBm |
| Transmit capacity, maximum | -3 dBm |
| Minimum receiver sensitivity | -21 dBm |
| Maximum receiver sensitivity | -3 dBm |
| Transmission physics | Single-mode fiberglass |
| Transmission length | 10 km (Fiberglass 9/125) |
| Wavelength | 1310 nm |
| Signal LEDs | depending on the Factoryline device |
| No. of channels | 1 (LC single mode) |

Product properties

| | |
|--------------|---|
| Product type | SFP module |
| Type | Factoryline devices with SFP slot |
| MTTF | 59 Years (Telcordia SR-332, temperature factor at 40°C = 1, stress factor at 50% = 1, environmental factor = 1) |
| Format | SFP (Small Form-factor Pluggable) |

Signaling

| | |
|----------------|--------------------------|
| Status display | via a Factoryline device |
|----------------|--------------------------|

Electrical properties

| | |
|---------------------|----|
| Transmission medium | FO |
|---------------------|----|

Environmental and real-life conditions

Ambient conditions

FL SFP LX10-B - Media module



1025401

<https://www.phoenixcontact.com/us/products/1025401>

| | |
|--|---|
| Degree of protection | IP20 |
| Ambient temperature (operation) | 0 °C ... 70 °C (non-condensing) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C (non-condensing) |
| Case temperature | max. 70 °C (Operation) |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 30 % ... 95 % (non-condensing) |
| Vibration (operation) | in acc. with IEC 60068-2-6: 5g, 150 Hz |
| Air pressure (operation) | 86 kPa ... 108 kPa (1500 m above sea level) |
| Air pressure (storage/transport) | 66 kPa ... 108 kPa (3500 m above sea level) |

Standards and regulations

| | |
|--------------------------|------------------------|
| Standard designation | Laser equipment safety |
| Standards/specifications | IEC 60825 |

FL SFP LX10-B - Media module



1025401

<https://www.phoenixcontact.com/us/products/1025401>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1025401>



cULus Recognized
Approval ID: E140403

FL SFP LX10-B - Media module



1025401

<https://www.phoenixcontact.com/us/products/1025401>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19179090 |
| ECLASS-15.0 | 19179090 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002608 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43222600 |
|-------------|----------|

FL SFP LX10-B - Media module



1025401

<https://www.phoenixcontact.com/us/products/1025401>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 3.96 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com