

LS-EMLP-AL (22X22) BK - Device marker



1027217

<https://www.phoenixcontact.com/us/products/1027217>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marker, Aluminum label, black (RAL 9005), unmarked, can be labeled with: TOPMARK LASER, TOPMARK NEO, mounting type: adhesive, Number of individual labels: 36, text field height: 22 mm, text field width: 22 mm



Your advantages

- Aluminum equipment marking for sticking on
- Identification made from metal, high strength in a lightweight design
- Increased durability due to the decoratively anodized surface

Commercial data

Item number	1027217
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BG19
Product key	BG241D
GTIN	4055626520827
Weight per piece (including packing)	80.32 g
Weight per piece (excluding packing)	77.88 g
Customs tariff number	76169990
Country of origin	CN

Technical data

Product properties

Product type	Device marker
Area of application	SIEMENS: SIRIUS ACT housing

Marking

Number of individual labels	36
Identification technology	Direct laser marking

Dimensions

Width	22 mm
Length	22 mm

Text field

Text field width	22 mm
Text field height	22 mm

Material specifications

RoHS compliant	yes
Adhesive strength	250 µm
Adhesive	Acrylic
Color	black (RAL 9005)
Base element material	Aluminum
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

LS-EMLP-AL (22X22) BK - Device marker



1027217

<https://www.phoenixcontact.com/us/products/1027217>

Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Salt spray test

Specification	ISO 9227:2012-05
Result	Test passed

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

LS-EMLP-AL (22X22) BK - Device marker



1027217

<https://www.phoenixcontact.com/us/products/1027217>

Classifications

ECLASS

ECLASS-13.0

27281103

ETIM

ETIM 9.0

EC001288

UNSPSC

UNSPSC 21.0

39131500

LS-EMLP-AL (22X22) BK - Device marker



1027217

<https://www.phoenixcontact.com/us/products/1027217>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com