

# SACC-M12MSL-4FECT-CL SH - Power connector



1027477

<https://www.phoenixcontact.com/us/products/1027477>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power connector, Power, 5-position, shielded, Plug straight M12, coding: L, Crimp connection, knurl material: Zinc die-cast, tin-plated, external cable diameter 8 mm ... 13 mm, without crimp contacts

## Your advantages

- Extremely compact, thanks to the small wiring space and high contact density
- Safely shielded: reliable shield connection even under extreme mechanical strain
- Robust connection: suitable for railway applications with high shock and vibration loads
- High-performance: DC connectors for up to 16 A and 63 V DC
- Protection against mismatching, thanks to special L-coding

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1027477       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF34          |
| Product key                          | AF2CJB        |
| GTIN                                 | 4055626521138 |
| Weight per piece (including packing) | 41.3 g        |
| Weight per piece (excluding packing) | 41.1 g        |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# SACC-M12MSL-4FECT-CL SH - Power connector



1027477

<https://www.phoenixcontact.com/us/products/1027477>

## Technical data

### Notes

|               |   |
|---------------|---|
| Assembly note | <b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
|---------------|---|


### Product properties

|                      |                                 |
|----------------------|---------------------------------|
| Product type         | Circular connector (cable-side) |
| Application          | Energy supply                   |
| Number of positions  | 5                               |
| No. of cable outlets | 1                               |
| Shielded             | yes                             |
| Coding               | L                               |
| Cable outlet         | straight                        |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Length              | 58 mm  |

### External dimensions

|                  |                |
|------------------|----------------|
| Outside diameter | 8 mm ... 13 mm |
|------------------|----------------|

### Housing

|                  |         |
|------------------|---------|
| Diameter housing | 21.5 mm |
|------------------|---------|

### Material specifications

|  |                              |
|--|------------------------------|
| Flammability rating according to UL 94 | V0                           |
| Material of grip body                  | Zinc die-cast, nickel-plated |
| Contact carrier material               | PA                           |
| Material for screw connection          | Zinc die-cast, tin-plated    |

### Connection data

#### Conductor connection

|                          |  |
|--------------------------|--|
| Connection method        | Crimp connection                                       |
| Connection cross section | 1.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (flexible) |

# SACC-M12MSL-4FECT-CL SH - Power connector



1027477

<https://www.phoenixcontact.com/us/products/1027477>

|                              |                                   |
|------------------------------|-----------------------------------|
| Connection cross section AWG | 14 (flexible)                     |
| Tightening torque            | M12 knurl                         |
|                              | Pressure nut with coupling sleeve |

## Connection assignment

|   |           |
|---|-----------|
| Contact   Color (signal designation)   Contact (optional) | 1 = BN    |
|   | 2 = WH    |
|   | 3 = BU    |
|   | 4 = BK    |
|   | FE = GYPK |

## Electrical properties

|                       |  |
|-----------------------|--|
| Rated surge voltage   | 1.5 kV   |
| Insulation resistance | $\geq 100 \text{ M}\Omega$                       |
| Nominal voltage $U_N$ | 63 V DC  |
| Nominal current $I_N$ | 16 A (when using 2.5 mm <sup>2</sup> conductors) |
|                       | 16 A (at 40 °C)                                  |

## Mechanical properties

### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

## Connector

### Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Plug     |
| Head cable outlet | straight |
| Head thread type  | M12      |
| Coding            | L        |

## Cable/line

|                      |       |
|----------------------|-------|
| Signal type/category | Power |
|----------------------|-------|

## Environmental and real-life conditions

### Ambient conditions

|   |                                  |
|---|----------------------------------|
| Degree of protection  | IP65                             |
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 85 °C (Plug / socket) |

## Standards and regulations

|                          |                              |
|--------------------------|------------------------------|
| Standard designation     | M12 connector                |
| Standards/specifications | according to IEC 61076-2-111 |

# SACC-M12MSL-4FECT-CL SH - Power connector




1027477

<https://www.phoenixcontact.com/us/products/1027477>


## Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Functional drawing




# SACC-M12MSL-4FECT-CL SH - Power connector

1027477

<https://www.phoenixcontact.com/us/products/1027477>



Schematic diagram



Pin assignment of M12 connector, 5-pos., L-coded, pin side view

# SACC-M12MSL-4FECT-CL SH - Power connector



1027477

<https://www.phoenixcontact.com/us/products/1027477>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1027477>

|  <b>cULus Recognized</b><br>Approval ID: E468743 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 600 V                 | 13 A                  | - 14              | -                           |

# SACC-M12MSL-4FECT-CL SH - Power connector



1027477

<https://www.phoenixcontact.com/us/products/1027477>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-M12MSL-4FECT-CL SH - Power connector



1027477

<https://www.phoenixcontact.com/us/products/1027477>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)