

# SACC-DSI-FS-5CON-M16-L180 PP - Device connector rear mounting



1027669

<https://www.phoenixcontact.com/us/products/1027669>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 5-position, Socket, straight, M12-Push-pull external locking, A-coding, Wave soldering, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Your advantages

- Established M12 standard for secure transmission of signals, data, and power
- Easy and quick cabling of devices and systems in hard-to-reach areas
- Manufacturer-independent M12 push-pull locking system for maximum availability
- Reliable shield connection even under extreme mechanical strain
- Compatible with connectors with screw or push-in connection

## Commercial data

Item number	1027669
Packing unit	12 pc
Minimum order quantity	12 pc
Note	Made to order (non-returnable)
Sales key	AB26
Product key	ABQEDJ
GTIN	4055626533391
Weight per piece (including packing)	26.09 g
Weight per piece (excluding packing)	18.209 g
Customs tariff number	85366990
Country of origin	DE

# SACC-DSI-FS-5CON-M16-L180 PP - Device connector rear mounting



1027669

<https://www.phoenixcontact.com/us/products/1027669>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	Lock nut is included in the scope of delivery
General	Push-pull external locking

### Mounting

Mounting type	Rear mounting (M16 x 1.5, with flat nut)
---------------	--

### Product properties

Product type	Circular connectors (device side)
Number of positions	5
Shielded	no
Coding	A
Thread type	M12

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Dimensions

Length of the solder pin	6 mm
	6 mm

### Material specifications

Material Housing	CuZn
Material Housing surface	Ni
Material Contact carrier	PA 6.6
Material Contact	CuZn
Material Contact surface	Au
Material Seal	NBR/FKM
Flammability rating according to UL 94	V0

### Electrical properties

Rated surge voltage	1.5 kV
Nominal voltage $U_N$	60 V
Nominal current $I_N$	4 A

### Connection data

# SACC-DSI-FS-5CON-M16-L180 PP - Device connector rear mounting



1027669

<https://www.phoenixcontact.com/us/products/1027669>

## Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Connector

### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	Push-pull external locking
Coding	A

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65 (When plugged in)
	IP67 (When plugged in)
	IP65/IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C
UL Type Rating	Type 4 (indoor use only)

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	based on IEC 61076-2-010

# SACC-DSI-FS-5CON-M16-L180 PP - Device connector rear mounting

1027669

<https://www.phoenixcontact.com/us/products/1027669>

## Drawings

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

# SACC-DSI-FS-5CON-M16-L180 PP - Device connector rear mounting



1027669

<https://www.phoenixcontact.com/us/products/1027669>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1027669>

 <b>cULus Recognized</b> Approval ID: E221474-20140616		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		60 V	4 A	-	-

# SACC-DSI-FS-5CON-M16-L180 PP - Device connector rear mounting



1027669

<https://www.phoenixcontact.com/us/products/1027669>

## Classifications

### ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

### ETIM

ETIM 10.0	EC003568
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSI-FS-5CON-M16-L180 PP - Device connector rear mounting



1027669

<https://www.phoenixcontact.com/us/products/1027669>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9e4d4415-129f-45b8-b3a6-06d6a4e74527

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)