

SAC-8P- 3,0-PVC/M12FS SH VA - Sensor/actuator cable



1037676

<https://www.phoenixcontact.com/us/products/1037676>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 8-position, PVC, black RAL 9005, shielded, free cable end, on Socket straight M12, coding: A, cable length: 3 m

Commercial data

Item number	1037676
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1CMA
GTIN	4055626571300
Weight per piece (including packing)	279.1 g
Weight per piece (excluding packing)	286.6 g
Country of origin	PL

SAC-8P- 3,0-PVC/M12FS SH VA - Sensor/actuator cable

1037676

<https://www.phoenixcontact.com/us/products/1037676>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	8
Shielded	yes

Connector

Connection 1

Type	free cable end
------	----------------


Connection 2

Type	Socket straight M12
Number of positions	8
Coding type	A

Cable/line

Cable length	3 m
--------------	-----

PVC black [PVC]

Dimensional drawing	
Note	The cable is not suitable for use with drag chains.
Cable weight	85 kg/km
UL AWM Style	2517
Number of positions	8
Shielded	yes
Cable type	PVC black [PVC]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross-section	8x 0.25 mm ² (Signal line)
Wire diameter incl. insulation	1.5 mm ±0.05 mm (Signal line)
External cable diameter	7.70 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material, filler	PVC
Material wire insulation	PVC

SAC-8P- 3,0-PVC/M12FS SH VA - Sensor/actuator cable



1037676

<https://www.phoenixcontact.com/us/products/1037676>

Single wire, color	white, brown, green, yellow, gray, pink, blue, red
Thickness, insulation	≥ 0.38 mm (Conductor insulation, signal line)
	≥ 0.76 mm (Outer cable sheath)
Overall twist	8 wires around filler to the core, twisted in with additional Cu litz in the wire outer godet
Optical shield covering	85 %
Max. conductor resistance	≤ 78 Ω/km
Insulation resistance	≥ 10 GΩ*km
Nominal voltage, cable	300 V
Test voltage	3000 V
Smallest bending radius, fixed installation	38.5 mm
Smallest bending radius, movable installation	77 mm
Flame resistance	According to UL 758/1581 (Cable Flame)
	According to DIN EN 60332-1-2 (60 s)
Resistance to oil	According to DIN EN 60811-2-1, 168 h at 80°C
Ambient temperature (operation)	-25 °C ... 105 °C (cable, fixed installation)

SAC-8P- 3,0-PVC/M12FS SH VA - Sensor/actuator cable





1037676

<https://www.phoenixcontact.com/us/products/1037676>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1037676>

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	2 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	2 A	-	-

SAC-8P- 3,0-PVC/M12FS SH VA - Sensor/actuator cable



1037676

<https://www.phoenixcontact.com/us/products/1037676>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-8P- 3,0-PVC/M12FS SH VA - Sensor/actuator cable



1037676

<https://www.phoenixcontact.com/us/products/1037676>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com