

# FOC-I-D1PGY-S/MPAGC - FO coupling



1041820

<https://www.phoenixcontact.com/us/products/1041820>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



FO coupling, degree of protection: IP20, number of positions: 2, material: Plastic, connection method: Coupling, cable outlet: straight, Ethernet

## Your advantages

- High reliability with comprehensive quality assurance measures
- Optimized precision (stability) with the use of ceramic sleeves
- Future-proof, thanks to RoHS 2 conformity
- Tailored for compatibility with the DIN rail adapters
- Assembly without special tools
- Flexible use, thanks to DIN rail and direct mounting
- Space-saving design
- With dust protection caps

## Commercial data

Item number	1041820
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIDA
GTIN	4055626598673
Weight per piece (including packing)	6.5 g
Weight per piece (excluding packing)	6.5 g
Customs tariff number	85367000
Country of origin	CN

## Technical data

### Notes

Notes on operation	For integration into DIN rail adapter NBC-PP-G1PGY
--------------------	--

### Product properties

Product type	Data plug
Type	FSMA
Number of positions	2
Connection profile	MTP: type A
No. of cable outlets	2
Number of slots	1
Cable outlet	straight

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated surge voltage	0.8 kV
Nominal current $I_N$	0.5 A
Transmission medium	FO

### Connection data

Connection method	Coupling
-------------------	----------

### Interfaces

Signal type/category	Ethernet
----------------------	----------

### Material specifications

Color of the housing part	beige
Flammability rating according to UL 94	V0
Housing material	Plastic
Contact material	Copper alloy

### Cable/line

Cable type	Fiberglass
Signal type/category	Ethernet
External sheath, color	silver-colored
Tensile strength short-term/long-term	40 N
Resistance to oil	no

### FO cable

Number of fibers	2
------------------	---

# FOC-I-D1PGY-S/MPAGC - FO coupling



1041820

<https://www.phoenixcontact.com/us/products/1041820>

## Mechanical properties

Tensile strength short-term/long-term	40 N
---------------------------------------	------

### Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-10 °C ... 70 °C
Resistance to UV radiation	no
Resistance to oil	no

## Standards and regulations

Resistance to oil	no
-------------------	----

## Mounting

Mounting type	Snap in
---------------	---------

# FOC-I-D1PGY-S/MPAGC - FO coupling



1041820

<https://www.phoenixcontact.com/us/products/1041820>

## Classifications

### ECLASS

ECLASS-13.0	19170116
ECLASS-15.0	19170116

### ETIM

ETIM 10.0	EC000752
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# FOC-I-D1PGY-S/MPAGC - FO coupling



1041820

<https://www.phoenixcontact.com/us/products/1041820>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)