

1043081

<https://www.phoenixcontact.com/us/products/1043081>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, PROFINET CAT5 (100 Mbps), 4-position, shielded, Plug straight M12 SPEEDCON, coding: D / IP65, on Plug angled M12 SPEEDCON, cable length: 0.8 m, For railway applications

Commercial data

Item number	1043081
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CJN
GTIN	4055626601885
Weight per piece (including packing)	82.9 g
Weight per piece (excluding packing)	82.9 g
Country of origin	PL

1043081

<https://www.phoenixcontact.com/us/products/1043081>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	4

Interfaces

Signal type/category	PROFINET CAT5, 100 Mbps
----------------------	-------------------------

Electrical properties

Transmission speed	100 Mbps
--------------------	----------

Material specifications

Outer sheath, material	PE-X
------------------------	------

Connector

Connection 1

Type	Plug straight M12 SPEEDCON / IP65
Number of positions	4
Locking type	SPEEDCON
Coding type	D (Data)
Shielded	yes
Handle color	black
Material	CuSn (Contact) Ni/Au (Contact surface) PA 6.6 (Contact carrier) PA 6.6 (Grip body) Zinc die-cast, nickel-plated (Screw connection)
Standards/regulations	PA 6.6: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)
Insertion/withdrawal cycles	≥ 100
Insulation resistance	≥ 100 MΩ
Tightening torque	0.4 Nm
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 85 °C

Connection 2

Type	Plug angled M12 SPEEDCON
Locking type	SPEEDCON

Cable/line

Cable length	0.8 m
Signal type/category	PROFINET CAT5, 100 Mbps
Outer sheath, material	PE-X

NBC-MSD/0,8-937/MRDC2 SCO RAIL - Network cable



1043081

<https://www.phoenixcontact.com/us/products/1043081>

External sheath, color	black RAL 9005
------------------------	----------------

1043081

<https://www.phoenixcontact.com/us/products/1043081>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

1043081

<https://www.phoenixcontact.com/us/products/1043081>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	1,6,7,8,9,14,15,16,17,17,18,18-Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]octadeca-7,15-diene ("Dechlorane Plus™")(CAS: n/a)
-------------------------------------	--

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com