


UT 4-L/HESI (5X20) GY - Fuse modular terminal block



1044423

<https://www.phoenixcontact.com/us/products/1044423>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse modular terminal block, fuse type: Glass / ceramics / ..., fuse type: G / 5 x 20, nom. voltage: 250 V, Thermal continuous current I_{th} : 28 A, connection method: Screw connection, Rated cross section: 4 mm², cross section: 0.14 mm²- 6 mm², connection method: Screw connection, Rated cross section: 4 mm², cross section: 0.14 mm²- 6 mm², mounting type: NS 35/7,5, NS 35/15, color: gray

Your advantages

- Globally recognized: Internationally proven screw connection
- Maintenance-free and vibration-resistant thanks to the patented Reakdyn principle
- Easy integration and replacement of fuses with the lever element
- Easy checking of the fuses with integrated test pick-offs
- Long-term stable connections with the use of high-quality materials
- Long-term stable connections with the use of high-quality materials
- Maximum efficiency in the smallest space - thanks to integrated level bridging, the connections are connected across levels

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1044423 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE01 |
| Product key | BE1136 |
| GTIN | 4055626622910 |
| Weight per piece (including packing) | 32.72 g |
| Weight per piece (excluding packing) | 32.1 g |
| Customs tariff number | 85369095 |
| Country of origin | PL |

UT 4-L/HESI (5X20) GY - Fuse modular terminal block



1044423

<https://www.phoenixcontact.com/us/products/1044423>

Technical data

Notes

| | |
|--------------------|---|
| Order information: | Fuse-link not supplied as standard |
| General | The current is determined by the fuse used, the voltage by the selected LED. If the fuse is faulty, the downstream circuit will not be disconnected. |

Product properties

| | |
|-----------------------|---------------------|
| Product type | Fuse terminal block |
| Product family | UT |
| Number of connections | 4 |
| Number of rows | 2 |
| Potentials | 2 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--|
| Fuse type | Glass / ceramics / ... |
| Rated surge voltage | 6 kV |
| Maximum power dissipation for nominal condition | 1.02 W |
| Fuse | G / 5 x 20 |
| Maximum power dissipation | max. 1.6 W (with single arrangement of the fuse terminal block in the event of overload) max. 1.6 W (With interconnected arrangement of several fuse terminal blocks in the event of overload) max. 4 W (with single arrangement of the fuse terminal block in the event of a short-circuit) max. 2.5 W (With interconnected arrangement of several fuse terminal blocks in the event of a short-circuit) |

Connection data

| | |
|---------------------------------|-------------------|
| Number of connections per level | 2 |
| Nominal cross section | 4 mm ² |

Level 1

| | |
|----------------------------------|-----------------------------|
| Connection method | Screw connection |
| Screw thread | M3 |
| Tightening torque | 0.6 ... 0.8 Nm |
| Stripping length | 9 mm |
| Internal cylindrical gage | A4 B3 |
| Connection in acc. with standard | IEC 60947-7-1/IEC 60947-7-3 |

UT 4-L/HESI (5X20) GY - Fuse modular terminal block



1044423

<https://www.phoenixcontact.com/us/products/1044423>

| | |
|---|--|
| Conductor cross-section rigid | 0.14 mm ² ... 6 mm ² |
| Cross section AWG | 26 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.14 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] | 26 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible ultrasound-compressed | 0.34 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] ultrasound-compressed | 22 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.14 mm ² ... 4 mm ² |
| 2 conductors with same cross section, rigid | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with same cross section, flexible | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm ² ... 1.5 mm ² |
| Nominal cross section | 4 mm ² |
| Thermal continuous current I _{th} | 28 A |
| Maximum load current | 36 A |
| Nominal voltage | 250 V |

Level 2

| | |
|---|--|
| Connection method | Screw connection |
| Screw thread | M3 |
| Tightening torque | 0.6 ... 0.8 Nm |
| Stripping length | 9 mm |
| Connection in acc. with standard | IEC 60947-7-1/IEC 60947-7-3 |
| Conductor cross-section rigid | 0.14 mm ² ... 6 mm ² |
| Cross section AWG | 26 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.14 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] | 26 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.14 mm ² ... 4 mm ² |
| 2 conductors with same cross section, rigid | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with same cross section, flexible | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm ² ... 1.5 mm ² |
| Nominal cross section | 4 mm ² |
| Nominal current | 6.3 A |
| Maximum load current | 6.3 A (the current is determined by the fuse used) |
| Nominal voltage | 500 V |

Ex data

Rated data (ATEX/IECEx)

| | |
|----------------|-----------------------|
| Identification | ⊕ II 3 G Ex ec IIC Gc |
|----------------|-----------------------|

UT 4-L/HESI (5X20) GY - Fuse modular terminal block



1044423

<https://www.phoenixcontact.com/us/products/1044423>

| | |
|-----------------------------|----------------------|
| Operating temperature range | -60 °C ... 130 °C |
| Ex-certified accessories | 1205053 SZS 0,6X3,5 |
| | 3022276 CLIPFIX 35-5 |
| | 3022218 CLIPFIX 35 |
| output | (Permanent) |

Ex connection data General

| | |
|--|--|
| Torque range | 0.6 Nm ... 0.8 Nm |
| Nominal cross section | 4 mm ² |
| Rated cross section AWG | 12 |
| Connection capacity rigid | 0.14 mm ² ... 6 mm ² |
| Connection capacity AWG | 26 ... 10 |
| Connection capacity flexible | 0.14 mm ² ... 6 mm ² |
| Connection capacity AWG | 26 ... 10 |
| 2 conductors with same cross section, solid | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with the same cross-section AWG rigid | 26 ... 16 |
| 2 conductors with same cross section, stranded | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with the same cross-section AWG flexible | 26 ... 16 |
| Conductor cross-section flexible, with ferrule without plastic sleeve min. | 0.14 mm ² |
| Conductor cross-section flexible, with ferrule without plastic sleeve max. | 4 mm ² |
| Single conductor/terminal point, flexible, with ferrule, without plastic sleeve, AWG | 26 ... 12 |
| output | (Permanent) |

Ex level Level 2

| | |
|----------------------|--------------------------------|
| Rated voltage | 500 V |
| Rated current | 20 A (4 mm ²) |
| Maximum load current | 20 A (6 mm ²) |
| Contact resistance | 0.6 mΩ |
| Temperature increase | 40 K (20 A/4 mm ²) |
| output | (Permanent) |

Ex level Level 3

| | |
|----------------------|----------------------------|
| Rated voltage | 250 V |
| Rated current | 6.3 A (4 mm ²) |
| Maximum load current | 6.3 A (6 mm ²) |
| Contact resistance | 5 mΩ |

Dimensions

| | |
|--------------------|---------|
| Width | 6.2 mm |
| Height | 92.7 mm |
| Depth | 94.5 mm |
| Depth on NS 35/7,5 | 88.9 mm |
| Depth on NS 35/15 | 96.4 mm |

UT 4-L/HESI (5X20) GY - Fuse modular terminal block



1044423

<https://www.phoenixcontact.com/us/products/1044423>

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Environmental and real-life conditions

Oscillation/broadband noise

| | |
|------------------------|--|
| Specification | DIN EN 50155 (VDE 0115-200):2008-03 |
| Spectrum | Long life test category 1, class B, body mounted |
| Frequency | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$ |
| ASD level | $0.964 \text{ (m/s}^2\text{)}^2\text{/Hz}$ |
| Acceleration | 0.58g |
| Test duration per axis | 5 h |
| Test directions | X-, Y- and Z-axis |
| Result | Test passed |

Shocks

| | |
|--------------------------------|-------------------------------------|
| Specification | DIN EN 50155 (VDE 0115-200):2008-03 |
| Pulse shape | Half-sine |
| Acceleration | 5g |
| Shock duration | 30 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |
| Result | Test passed |

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |

UT 4-L/HESI (5X20) GY - Fuse modular terminal block



1044423

<https://www.phoenixcontact.com/us/products/1044423>

| | |
|--|-----------------|
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|-----------------------------|
| Connection in acc. with standard | IEC 60947-7-1/IEC 60947-7-3 |
| | IEC 60947-7-1/IEC 60947-7-3 |

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |

UT 4-L/HESI (5X20) GY - Fuse modular terminal block




1044423

<https://www.phoenixcontact.com/us/products/1044423>

Drawings

Circuit diagram



UT 4-L/HESI (5X20) GY - Fuse modular terminal block





1044423


<https://www.phoenixcontact.com/us/products/1044423>


Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1044423>

|  CSA Approval ID: 13631 | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | | | | |
| upper level | 300 V | 16 A | 26 - 10 | - |
| lower level | 300 V | 20 A | 26 - 10 | - |
| C | | | | |
| upper level | 300 V | 16 A | 26 - 10 | - |
| lower level | 300 V | 20 A | 26 - 10 | - |

|  cULus Recognized Approval ID: E60425 | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | | | | |
| upper level | 300 V | 16 A | 26 - 10 | - |
| lower level | 300 V | 20 A | 26 - 10 | - |
| C | | | | |
| upper level | 300 V | 16 A | 26 - 10 | - |
| lower level | 300 V | 20 A | 26 - 10 | - |

|  cUL Recognized Approval ID: E192998 | | | | |
|---|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| with cartridge fuse-link | 300 V | 16 A | 26 - 10 | 26 - 10 |
| middle level | 300 V | 20 A | 26 - 10 | 26 - 10 |

|  IECEx Approval ID: IECExKIWA14.0014U | | | | |
|--|--|--|--|--|
|--|--|--|--|--|

|  UL Recognized Approval ID: E192998 | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| with cartridge fuse-link | 300 V | 16 A | 26 - 10 | - |
| middle level | 300 V | 20 A | 26 - 10 | - |

UT 4-L/HESI (5X20) GY - Fuse modular terminal block



1044423

<https://www.phoenixcontact.com/us/products/1044423>



CCC

Approval ID: 2020322313000632



ATEX

Approval ID: KIWA14ATEX0025U



UKCA-EX

Approval ID: CSAFE 21UKEX3606U



EAC Ex

Approval ID: KZ 7500525010101950

UT 4-L/HESI (5X20) GY - Fuse modular terminal block



1044423

<https://www.phoenixcontact.com/us/products/1044423>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250113 |
| ECLASS-15.0 | 27250113 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000899 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

UT 4-L/HESI (5X20) GY - Fuse modular terminal block



1044423

<https://www.phoenixcontact.com/us/products/1044423>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 420639af-3bbf-4608-8a8e-a77d74745e4d |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.232 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com