# WS-DIO PT 2,5 - Warning label

1029037

https://www.phoenixcontact.com/us/products/1029037

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Warning label, Mixed color, labeled: Diode, mounting type: plug in, for terminal block width: 5.2 mm

## Your advantages

- Mains terminal blocks are reliably covered and marked using warning labels
- Accidental actuation of the terminal points is therefore prevented

## Commercial data

| | |
|---|---|
| Item number | 1029037 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE22 |
| Product key | BE224Z |
| GTIN | 4055626529974 |
| Weight per piece (including packing) | 1.1 g |
| Weight per piece (excluding packing) | 1.1 g |
| Customs tariff number | 49119900 |
| Country of origin | IN |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Warning label printed |
| Type | Rectangle |
| Number of positions | 5 |
| Pitch | 5.2 mm |

Marking

| | |
|---|---|
| Printing | Diode |

### Dimensions

| | |
|---|---|
| Width | 4.60 mm |
| Height | 6.30 mm |
| Depth | 6.50 mm |
| Pitch | 5.2 mm |

### Material specifications

| | |
|---|---|
| Color | multicolored (RAL -) |
| | yellow (RAL 1018) |
| | black (RAL 9005) |
| Material | PA |
| Flammability rating according to UL 94 | V0 |
| Components | free from silicone and halogen |

### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

### Standards and regulations

| | |
|---|---|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |

### Mounting

| | |
|---|---|
| Mounting type | plug in |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 40200507 |
| ECLASS-15.0 | 27281107 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC001777 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 55121700 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com