


# FTP-3/4SL - Test plug



1030004

<https://www.phoenixcontact.com/us/products/1030004>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug, nom. voltage: 400 V, nominal current: 20 A, number of positions: 4, connection method: Cable lug connection, Rated cross section: 2.5 mm<sup>2</sup>, color: gray

## Your advantages

- Space saving, thanks to offset test socket arrangement
- Easy and time saving, thanks to functional grouping of switching operations
- Cost-effective, thanks to the tailored, modular design and use of standardized CLIPLINE complete accessories
- The automatically generated transformer short circuit and the shock-proof design ensure the highest degree of safety during measurement
- The integrated, robust switch contact is designed for the most stringent demands, and the use of high-quality materials ensures the transmission of signal currents, even after multiple actuations
- Maximum safety with leading and automatic transformer short circuit

## Commercial data

Item number	1030004
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BE6113
GTIN	4055626532523
Weight per piece (including packing)	176.3 g
Weight per piece (excluding packing)	176.1 g
Country of origin	PL

# FTP-3/4SL - Test plug



1030004

<https://www.phoenixcontact.com/us/products/1030004>

## Technical data

### Product properties

Product type	Test plug terminal block
Product family	FAME 3 SL
Number of positions	4
Pitch	8.2 mm
Potentials	4

### Electrical properties

Maximum power dissipation for nominal condition	1.31 W
-------------------------------------------------	--------

### Connection data

Nominal cross section	6 mm <sup>2</sup>
Test socket torque	0.5
Connection method	Cable lug connection
Conductor cross-section flexible	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	20 ... 14 (converted acc. to IEC)
Nominal cross section	2.5 mm <sup>2</sup>
Nominal current	20 A
Maximum load current	20 A
Nominal voltage	400 V

### Dimensions

Width	56.8 mm
Height	96.8 mm
Depth	98.2 mm
Pitch	8.2 mm

### Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# FTP-3/4SL - Test plug


1030004

<https://www.phoenixcontact.com/us/products/1030004>



## Drawings

Circuit diagram



# FTP-3/4SL - Test plug



1030004

<https://www.phoenixcontact.com/us/products/1030004>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1030004>



**cULus Recognized**  
Approval ID: E60425



**cULus Recognized**  
Approval ID: E60425

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
F				
	690 V	31 A	-	-

# FTP-3/4SL - Test plug



1030004

<https://www.phoenixcontact.com/us/products/1030004>

## Classifications

### ECLASS

ECLASS-13.0	27250304
ECLASS-15.0	27250304

### ETIM

ETIM 10.0	EC002555
-----------	----------

### UNSPSC

UNSPSC 21.0	20122000
-------------	----------

# FTP-3/4SL - Test plug



1030004

<https://www.phoenixcontact.com/us/products/1030004>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)