

SAC-5P- 2,0-PVC/M12FS AE - Sensor/actuator cable



1033768

<https://www.phoenixcontact.com/us/products/1033768>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, PVC, black RAL 9005, free cable end, on Socket straight M12, coding: A, cable length: 5 m, with ferrules

Commercial data

Item number	1033768
Packing unit	1 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	AF1CDA
GTIN	4055626540535
Weight per piece (including packing)	93.6 g
Weight per piece (excluding packing)	22.22 g
Country of origin	PL

SAC-5P- 2,0-PVC/M12FS AE - Sensor/actuator cable



1033768

<https://www.phoenixcontact.com/us/products/1033768>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	5

Connector

Connection 1

Type	free cable end
------	----------------


Connection 2

Type	Socket straight M12
Number of positions	5
Coding type	A

Cable/line

Cable length	5 m
--------------	-----

PVC black [PVC]

Dimensional drawing	
Cable weight	51 kg/km
UL AWM Style	2464 / 1729 (80°C/300 V)
Number of positions	5
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	19x 0.15 mm
AWG signal line	22
Conductor cross-section	5x 0.34 mm ² (Signal line)
Wire diameter incl. insulation	1.26 mm ±0.05 mm
External cable diameter	5.00 mm ±0.15 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, white, blue, black, green-yellow
Thickness, insulation	≥ 0.23 mm (Core insulation)
Thickness, outer sheath	≥ 0.76 mm

SAC-5P- 2,0-PVC/M12FS AE - Sensor/actuator cable



1033768

<https://www.phoenixcontact.com/us/products/1033768>

Overall twist	5 wires around filler to the core
Max. conductor resistance	max. 57 Ω /km (at 20 °C)
Insulation resistance	\geq 200 M Ω *km (at 20 °C)
Nominal voltage, cable	\leq 300 V
Test voltage	\geq 3000 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	25 mm
Smallest bending radius, movable installation	50 mm
Flame resistance	UL VW-1
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -10 °C ... 80 °C (Cable, flexible installation)

SAC-5P- 2,0-PVC/M12FS AE - Sensor/actuator cable



1033768

<https://www.phoenixcontact.com/us/products/1033768>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P- 2,0-PVC/M12FS AE - Sensor/actuator cable



1033768

<https://www.phoenixcontact.com/us/products/1033768>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com