# HC-B24/16-ADP-SS - Adapter plate

1034216

https://www.phoenixcontact.com/us/products/1034216

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Adapter plate, design: B24 to B16



## Commercial data

| | |
|---|---|
| Item number | 1034216 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF66 |
| Product key | AF7AZD |
| GTIN | 4055626540627 |
| Weight per piece (including packing) | 106.5 g |
| Weight per piece (excluding packing) | 104 g |
| Customs tariff number | 73269098 |
| Country of origin | DE |

## Technical data


### Notes

| | |
|---|---|
| General | For wall cutouts of type B24 |

### Product properties

| | |
|---|---|
| Product type | Adapter plate |
| Type | B24 |
| Seal present | yes |

### Dimensions

| | |
|---|---|
| Dimensional drawing |  |
| Width | 53 mm |
| Height | 5 mm |
| Length | 151 mm |
| Drill hole distance, horizontal | 130 mm |
| Drill hole distance, vertical | 32 mm |
| Hole diameter | 5.5 mm |

### Material specifications

| | |
|---|---|
| Material | Stainless steel 1.4301/AISI 304 |
| Material grommet GRP | NBR/SBR (Flat gasket) |

### Environmental and real-life conditions

Ambient conditions


| | |
|---|---|
| Degree of protection | IP54 |
| | IP65 |
| Ambient temperature (operation) | -40 °C ... 125 °C |

### Mounting

| | |
|---|---|
| Assembly note | Torque of the mounting screws 1 ... 2 Nm |

## Drawings

Dimensional drawing




Dimensional drawing

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440201 |
| ECLASS-15.0 | 27440201 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002309 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 31261500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 4.146 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com