

NBC-M12MSD/2,37-93B CV - Network cable



1036682

<https://www.phoenixcontact.com/us/products/1036682>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, PROFINET CAT5, 4-position, shielded, Plug straight M12, coding: D / IP67, on free cable end, cable length: 2.37 m, Pre-construction stage

Commercial data

Item number	1036682
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CMI
GTIN	4055626569338
Weight per piece (including packing)	167.3 g
Weight per piece (excluding packing)	167 g
Country of origin	PL

NBC-M12MSD/2,37-93B CV - Network cable



1036682

<https://www.phoenixcontact.com/us/products/1036682>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	4

Interfaces

Signal type/category	PROFINET CAT5 (IEC 11801)
----------------------	---------------------------

Material specifications

Outer sheath, material	PVC
------------------------	-----

Connector

Connection 1

Type	Plug straight M12 / IP67
Coding type	D
Degree of protection	IP67

Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	2.37 m
Signal type/category	PROFINET CAT5 (IEC 11801)
Outer sheath, material	PVC
External sheath, color	green RAL 6018
Material, inner sheath	PVC

NBC-M12MSD/2,37-93B CV - Network cable



1036682

<https://www.phoenixcontact.com/us/products/1036682>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

NBC-M12MSD/2,37-93B CV - Network cable



1036682

<https://www.phoenixcontact.com/us/products/1036682>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com