

# NBC-M12MSD/ 2,0-93C - Network cable



1038747

<https://www.phoenixcontact.com/us/products/1038747>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, PROFINET CAT5 (100 Mbps), EtherCAT® CAT5 (100 Mbps), 4-position, PUR halogen-free, green RAL 6018, shielded (Advanced Shielding Technology), Plug straight M12, coding: D / IP67, on free cable end, cable length: 2 m

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1038747       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF04          |
| Product key                          | AF1CJN        |
| GTIN                                 | 4055626592084 |
| Weight per piece (including packing) | 151.4 g       |
| Weight per piece (excluding packing) | 142.44 g      |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

1038747

<https://www.phoenixcontact.com/us/products/1038747>

## Technical data

### Product properties

|                     |                         |
|---------------------|-------------------------|
| Product type        | Data cable preassembled |
| Application         | Standard                |
| Number of positions | 4                       |
| Shielded            | yes                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Interfaces

|                      |   |
|----------------------|---|
| Bus system           | PROFINET  |
| Signal type/category | PROFINET CAT5 (IEC 11801), 100 Mbps<br>EtherCAT® CAT5 (IEC 11801), 100 Mbps |

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Electrical properties


|   |                       |
|---|-----------------------|
| Nominal voltage $U_N$                   | 48 V AC               |
|   | 60 V DC               |
| Nominal current $I_N$                   | 4 A                   |
| Transmission medium                     | Copper                |
| Transmission speed                      | 100 Mbps              |
| Transmission characteristics (category) | CAT5 (IEC 11801:2002) |

### Material specifications

|  |    |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

### Connector

#### Connection 1

|                     |   |
|---------------------|---|
| Dimensional drawing |  <p>Pin assignment M12 male connector, 4-pos., D-coded, male side</p> |
| Type                | M12 Plug, straight, 4-position, shielded (Advanced Shielding Technology), Keying: D   |
| Number of positions | 4   |

# NBC-M12MSD/ 2,0-93C - Network cable



1038747

<https://www.phoenixcontact.com/us/products/1038747>

|  |   |
|--|---|
| Shielded                               | yes   |
| Shielding                              | Advanced Shielding Technology                                     |
| Signal type/category                   | EtherCAT® CAT5 (IEC 11801), 100 Mbps<br>PROFINET CAT5 (IEC 11801) |
| Insertion/withdrawal cycles            | ≥ 100   |
| Insulation resistance                  | ≥ 100 MΩ  |
| Overvoltage category                   | II  |
| Degree of pollution                    | 3   |
| Tightening torque                      | 0.4 Nm  |
| Material Contact                       | CuSn  |
| Material Contact surface               | Ni/Au   |
| Material Contact carrier               | PA 6.6  |
| Material Screw connection              | Die-cast zinc, nickel-plated                                      |
| Material Grip body                     | TPU, hardly inflammable, self-extinguishing                       |
| Material Seal                          | FKM   |
| Flammability rating according to UL 94 | V0  |
| Degree of protection                   | IP65<br>IP67  |
| Ambient temperature (operation)        | -25 °C ... 85 °C  |
| Standard designation                   | M12 connector   |
| Standards/regulations                  | IEC 61076-2-101   |


## Connection 2

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

## Cable/line

|              |     |
|--------------|-----|
| Cable length | 2 m |
|--------------|-----|

## PROFINET drag chain CAT5 [93C]

|                                |  |
|--------------------------------|--|
| Dimensional drawing            |  |
| UL AWM Style                   | 20233 (80°C/300 V)   |
| Number of positions            | 4  |
| Shielded                       | yes  |
| Cable type                     | PROFINET drag chain CAT5 [93C]   |
| Conductor structure            | 1x4xAWG22/7, SF/TQ   |
| AWG signal line                | 22   |
| Conductor cross-section        | 4x 0.34 mm <sup>2</sup>  |
| Wire diameter incl. insulation | 1.5 mm ±0.05 mm  |

# NBC-M12MSD/ 2,0-93C - Network cable



1038747

<https://www.phoenixcontact.com/us/products/1038747>

|   |   |
|---|---|
| External cable diameter                       | 6.50 mm ±0.2 mm   |
| Outer sheath, material                        | PUR   |
| External sheath, color                        | green RAL 6018  |
| Conductor material                            | Tin-plated Cu litz wires  |
| Material wire insulation                      | PE  |
| Single wire, color                            | white, yellow, blue, orange   |
| Overall twist                                 | Star quad   |
| Optical shield covering                       | 85 %  |
| Insulation resistance                         | ≥ 500 MΩ*km   |
| Loop resistance                               | ≤ 120.00 Ω/km   |
| Wave impedance                                | 100 Ω ±15 Ω (at 1 ... 100 MHz)  |
| Nominal voltage, cable                        | ≤ 300 V   |
| Test voltage Core/Core                        | 2000 V (50 Hz, 1 min.)  |
| Test voltage Core/Shield                      | 2000.00 V (50 Hz, 1 min.)   |
| Minimum bending radius, fixed installation    | 5 x D   |
| Minimum bending radius, flexible installation | 7.5 x D   |
| Dynamic load capacity (bending)               | Max. bending cycles: 3000000, Bending radius: 200 mm, Traversing path: 10 m, Traversing rate: 4 m/s, Acceleration: 4 m/s <sup>2</sup> |
| Dynamic load capacity (torsion)               | Torsion: ±30 °/m  |
| Halogen-free                                  | according to IEC 60754-1  |
| Flame resistance                              | according to IEC 60332-1-2<br>in accordance with UN ECE-R 118.03<br>according to CSA C 22.2 No. 210-FT1                               |
| Resistance to oil                             | in accordance with DIN EN 60811-404   |
| Other resistance                              | UV resistant  |
| Special properties                            | Flexible cable conduit capable  |
| Ambient temperature (operation)               | -40 °C ... 70 °C (cable, fixed installation)<br>-40 °C ... 70 °C (Cable, flexible installation)                                       |

## Environmental and real-life conditions

### Ambient conditions

|                      |  |
|----------------------|--|
| Degree of protection | IP65 (M12 connector)<br>IP67 (M12 connector) |
|----------------------|--|

## Standards and regulations

### M12

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |

Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Schematic diagram



Pin assignment M12 male connector, 4-pos., D-coded, male side


# NBC-M12MSD/ 2,0-93C - Network cable



1038747

<https://www.phoenixcontact.com/us/products/1038747>

Circuit diagram



Contact assignment of the M12 plug

# NBC-M12MSD/ 2,0-93C - Network cable




1038747

<https://www.phoenixcontact.com/us/products/1038747>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1038747>

|  <b>cULus Listed</b><br>Approval ID: E335024 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 250 V                 | 4 A                   | -                 | -                           |

# NBC-M12MSD/ 2,0-93C - Network cable



1038747

<https://www.phoenixcontact.com/us/products/1038747>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# NBC-M12MSD/ 2,0-93C - Network cable



1038747

<https://www.phoenixcontact.com/us/products/1038747>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)