

FOC-I-D1PGY-S/MPBGC - FO coupling



1041840

<https://www.phoenixcontact.com/us/products/1041840>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



FO coupling, degree of protection: IP20, number of positions: 2, material: Plastic, connection method: Coupling, cable outlet: straight, Ethernet

Your advantages

- High reliability with comprehensive quality assurance measures
- Optimized precision (stability) with the use of ceramic sleeves
- Future-proof, thanks to RoHS 2 conformity
- Tailored for compatibility with the DIN rail adapters
- Assembly without special tools
- Flexible use, thanks to DIN rail and direct mounting
- Space-saving design
- With dust protection caps

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1041840 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB16 |
| Product key | ABNIDA |
| GTIN | 4055626598680 |
| Weight per piece (including packing) | 7.9 g |
| Weight per piece (excluding packing) | 7.9 g |
| Customs tariff number | 85367000 |
| Country of origin | CN |

Technical data

Notes

| | |
|--------------------|--|
| Notes on operation | For integration into DIN rail adapter NBC-PP-G1PGY |
|--------------------|--|

Product properties

| | |
|----------------------|-------------|
| Product type | Data plug |
| Type | FSMA |
| Sensor type | Ethernet |
| Number of positions | 2 |
| Connection profile | MTP: type B |
| No. of cable outlets | 2 |
| Number of slots | 1 |
| Cable outlet | straight |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 2 |

Electrical properties

| | |
|-----------------------|--------|
| Rated surge voltage | 0.8 kV |
| Nominal current I_N | 0.5 A |
| Transmission medium | FO |

Connection data

| | |
|-------------------|----------|
| Connection method | Coupling |
|-------------------|----------|

Material specifications

| | |
|--|--------------|
| Color of the housing part | beige |
| Flammability rating according to UL 94 | V0 |
| Housing material | Plastic |
| Contact material | Copper alloy |

Cable/line

| | |
|---------------------------------------|----------------|
| Cable type | Fiberglass |
| External sheath, color | silver-colored |
| Tensile strength short-term/long-term | 40 N |
| Resistance to oil | no |

FO cable

| | |
|------------------|---|
| Number of fibers | 2 |
|------------------|---|

Mechanical properties

| | |
|---------------------------------------|------|
| Tensile strength short-term/long-term | 40 N |
|---------------------------------------|------|

FOC-I-D1PGY-S/MPBGC - FO coupling



1041840

<https://www.phoenixcontact.com/us/products/1041840>

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 500 |
|-----------------------------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Degree of protection | IP20 |
| | IP20 |
| Ambient temperature (operation) | -10 °C ... 70 °C |
| Resistance to UV radiation | no |
| Resistance to oil | no |

Standards and regulations

| | |
|-------------------|----|
| Resistance to oil | no |
|-------------------|----|

Mounting

| | |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

FOC-I-D1PGY-S/MPBGC - FO coupling



1041840

<https://www.phoenixcontact.com/us/products/1041840>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19170116 |
| ECLASS-15.0 | 19170116 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000752 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

FOC-I-D1PGY-S/MPBGC - FO coupling



1041840

<https://www.phoenixcontact.com/us/products/1041840>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com