

H5S:3C5FF:GF - Housing



1046947

<https://www.phoenixcontact.com/us/products/1046947>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYPORT B48 panel mounting base, with single screw lock, with plastic protective cover, with stainless steel front plate connections 3x RJ45 CAT5e (female/female) 1x D-SUB 9 (female/female), 1x 120 V duplex outlet 5 A - GFCI 20 A

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1046947 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF69 |
| Product key | AF7EGX |
| GTIN | 4055626645858 |
| Weight per piece (including packing) | 22.22 g |
| Weight per piece (excluding packing) | 22.22 g |
| Country of origin | US |

H5S:3C5FF:GF - Housing

1046947

<https://www.phoenixcontact.com/us/products/1046947>

Technical data

Product properties

| | |
|------------------|-----------------------|
| Product type | Stackable housing set |
| Application | Standard |
| Type | B48 |
| Protective cover | yes |


Electrical properties

| | |
|-----------------------|---|
| Rated voltage (III/3) | max. 125 V AC (AC outlet, UL 498, UL 943, CSA C22.2 No. 42) |
| Rated current | max. 1.5 A DC (RJ45) |
| | 20 A (AC outlet, UL 498, UL 943, CSA C22.2 No. 42) |

Connection data

| | |
|-------------------|--------------|
| Tightening torque | 1.5 ... 2 Nm |
|-------------------|--------------|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 99.2 mm |
| Height | 39.4 mm |
| Length | 162 mm |

Material specifications

| | |
|----------------------------|---|
| Material | Stainless steel (Front plate) |
| Seal material | NBR, conductive |
| | NBR, conductive |
| Housing material | Die-cast aluminum, salt water resistant |
| Housing surface material | uncoated |
| Material, protective cover | PA |
| Locking latch material | Stainless steel |

Connector

| | |
|-----------------------|--|
| Contact insert design | with 3x RJ45 Cat 5E Ethernet Socket/socket, snap-in slot locking |
| | with 1x 120 V AC outlet 5 A GFCI 20 A GFCI 20 A |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-----------------------------|
| Degree of protection | IP65 |
| Impact strength | IK08 |
| Ambient temperature (operation) | -40 °C ... 125 °C (Housing) |

H5S:3C5FF:GF - Housing


1046947

<https://www.phoenixcontact.com/us/products/1046947>




Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing



Mounting cutout

H5S:3C5FF:GF - Housing



1046947

<https://www.phoenixcontact.com/us/products/1046947>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440113 |
| ECLASS-15.0 | 27440113 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002636 |
|----------|----------|

H5S:3C5FF:GF - Housing



1046947

<https://www.phoenixcontact.com/us/products/1046947>

Environmental product compliance

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com