

IOA PR-DAI/DAO/F/DS/2A/EX - Input/output module



1048208

<https://www.phoenixcontact.com/us/products/1048208>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse module for VIP I/O marshalling base elements with replaceable 2 A fuse in the field device supply path. Integrated test points and a disconnect knife allow uninterrupted signal measurement. HART transparent.

Product description

Fuse module with replaceable 2 A fuse in the supply path. This enables field devices to be supplied with voltage directly from the base element. If the fuse fails, this is indicated by an LED. Test points and a disconnect knife are available in the signal path for uninterrupted signal measurement. The module is installed on a corresponding VIP I/O-Marshalling base element by means of plug-in contact. Installation in zone 2, "ec" type of protection is permitted.

Commercial data

Item number	1048208
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C480
Product key	DK115A
GTIN	4055626649948
Weight per piece (including packing)	64.3 g
Weight per piece (excluding packing)	64.3 g
Customs tariff number	85371098
Country of origin	US

1048208

<https://www.phoenixcontact.com/us/products/1048208>

Technical data

Product properties

Product type	Interface module
Product family	VIP I/O-Marshalling
Number of positions	1

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage U_{\max}	≤ 30 V
Current	≤ 1 A (Signal)
Current ()	≤ 2 A (Current limited by fuse)
	≤ 3 A

Ex data

Safety data

Input voltage U_i	30 V
Input current I_i	1 A
Inductance L_i	0 mH
Capacitance C_i	0 μ F
Max. output voltage U_o	U_i
Max. output current I_o	I_i
Max. output power P_o	P_i

Interfaces

Data communication (bypass)

HART function	HART transparency
Protocols supported	HART

Dimensions

Item dimensions

Width	10.3 mm
Height	64.2 mm
Depth	72.9 mm

Material specifications

Color	gray (RAL 7042)
-------	-----------------

Environmental and real-life conditions

IOA PR-DAI/DAO/F/DS/2A/EX - Input/output module



1048208

<https://www.phoenixcontact.com/us/products/1048208>

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C
Altitude	≤ 2000 mm
Permissible humidity (operation)	0 % ... 95 % (non-condensing)

Approvals

ATEX

Identification	⊕ II 3G Ex ec IIC T4 Gc
	⊕ II 3G Ex ic IIC T4 Gc
Certificate	CSANe 20ATEX3152X

IECEX

Identification	Ex ec IIC T4 Gc
	Ex ic IIC T4 Gc
Certificate	IECEX SIR 21.0005X

UKEX

Identification	⊕ II 3G Ex ec IIC T4 Gc
	⊕ II 3G Ex ic IIC T4 Gc
Certificate	PxCIF23UKEX1048208X

CSA, USA/Canada

Identification	Class I, Div. 2, Groups A, B, C, D
	Class I, Zone 2, AEx ic IIC T4 Gc
	ANIFW apparatus for connection to: Class I, II, III, Div. 2 Groups A, B, C, D, F, G
	Ex ic IIC T4 Gc
Certificate	Ex ec IIC T4 Gc
	CSA 21CA80047687X

Standards and regulations


Standards/regulations	IEC 60664
	DIN EN 50178

Mounting

Mounting type	Plug-in mounting
Assembly note	Plugs into VIP/...BASE...
Mounting position	any

Drawings

Schematic diagram



1048208

<https://www.phoenixcontact.com/us/products/1048208>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1048208>

Functional Safety

Approval ID: PHO 16-09-035



IECEX

Approval ID: IECEx SIR 21.0005X



ATEX

Approval ID: CSANe 20ATEX3152X



CSA

Approval ID: 80047687



CSAus

Approval ID: 80047687

1048208

<https://www.phoenixcontact.com/us/products/1048208>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 10.0	EC002780
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1048208

<https://www.phoenixcontact.com/us/products/1048208>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	66216299-b8b6-45e8-afde-0baced4e9ac8

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com