

PV-C1F-C-HSG - Photovoltaic connector



1050771

<https://www.phoenixcontact.com/us/products/1050771>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Photovoltaic connector, Range of articles: SUNCLIX, color: black, number of positions: 1, min. conductor cross-section: 2.5 mm², max. conductor cross-section: 6 mm², rated voltage: 1500 V DC, rated current: 51 A, Connection method: Crimp, min. cable diameter: 5 mm, max. cable diameter: 8 mm

Your advantages

- Crimp connection technology for automated assembly processes
- High yield, thanks to silver-plated contacts
- International approvals in accordance with IEC and UL enable worldwide use
- Unique SUNCLIX pin connector pattern

Commercial data

Item number	1050771
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AB02
Product key	ABLBBB
GTIN	4055626669632
Weight per piece (including packing)	9.821 g
Weight per piece (excluding packing)	9.821 g
Customs tariff number	85359000
Country of origin	IN

Technical data

Notes

Safety note

Safety note	<ul style="list-style-type: none"> • WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.
	<ul style="list-style-type: none"> • WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.
	<p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p>
	<ul style="list-style-type: none"> • The products are suitable for applications in plant, controller, and electrical device engineering.
	<ul style="list-style-type: none"> • Assembled products may not be manipulated or improperly opened.
	<ul style="list-style-type: none"> • Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).
	<ul style="list-style-type: none"> • When using the product in direct connection with third-party manufacturers, the user is responsible.
	<ul style="list-style-type: none"> • For operating voltages > 50 V AC, conductive connector housings must be grounded
	<ul style="list-style-type: none"> • Ensure that the protective or functional ground has been properly connected.
	<ul style="list-style-type: none"> • Observe the corresponding technical data. You will find information: <ul style="list-style-type: none"> o On the product o On the packing label o In the supplied documentation o Online at phoenixcontact.com/products under the product
	<ul style="list-style-type: none"> • The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.
	<ul style="list-style-type: none"> • Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at phoenixcontact.com/products
	<ul style="list-style-type: none"> • The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).
	<ul style="list-style-type: none"> • Operate the connector only when it is fully plugged in and interlocked.
	<ul style="list-style-type: none"> • Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.

PV-C1F-C-HSG - Photovoltaic connector



1050771

<https://www.phoenixcontact.com/us/products/1050771>

• Observe the minimum bending radius of the cable. Lay the cable without twisting it.

Product properties

Product type	Photovoltaic connectors
Product family	SUNCLIX
Number of positions	1

Insulation characteristics

Protection class	II
Degree of pollution	2

Electrical properties

Rated voltage (II/2)	1500 V
Nominal voltage ATD	1500 V DC (II/2.00) in accordance with IEC 62852:2014/AMD1:2020
	1500 V DC in accordance with UL 6703
Rated surge voltage	16 kV
Rated surge voltage (III/3)	16 kV
Rated current (10 mm ²)	51 A (in accordance with IEC 62852:2014/AMD1:2020)
Rated current (6.0 mm ²)	40 A (in accordance with IEC 62852:2014/AMD1:2020)
Rated current (4.0 mm ²)	34 A (in accordance with IEC 62852:2014/AMD1:2020)
Rated current (2.5 mm ²)	27 A (in accordance with IEC 62852:2014/AMD1:2020)
Rated current	50 A (in accordance with UL 6703)
	35 A (in accordance with UL 6703)
	30 A (in accordance with UL 6703)
Contact resistance	≤ 0.45 mΩ
Contact resistance	< 0.3 mΩ (Crimp to crimp)

Connection data

Connection method	Crimp
Stripping length	8 mm

Dimensions

Width	20 mm
Height	20 mm
Length	72.8 mm

Material specifications

Color	black
Color of the housing part	black
Material Housing	PPE
Material Contact	Cu
Flammability rating according to UL 94	V0
Insulating material group	II
Insulating material	mPPE

PV-C1F-C-HSG - Photovoltaic connector



1050771

<https://www.phoenixcontact.com/us/products/1050771>

Cable seal material	EPDM
Contact surface material	Ag
O-ring material	Silopren LSR 2660

Cable/line

External cable diameter	5 mm ... 8 mm
External cable diameter	5 mm ... 8 mm
Single wire, cross section	2.5 mm ² 6 mm ² 14 AWG 10 AWG
Stripping length of the individual wire	9 mm -1 mm
Cable pull-out force	> 80 N (IEC 62852:2014)

Mechanical properties

Outside conductor diameter	5.00 mm 8.00 mm
----------------------------	-----------------

Mechanical data

Outside conductor diameter	5.00 mm 8.00 mm
Insertion/withdrawal cycles	100
Insertion force	45 N ±10 N
Withdrawal force	250 N ±50 N (when locked)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66/IP68 (2 m / 24 h) (plugged in)
	IP20 (Not plugged in)
	IP66/IP68 (2 m / 24 h)
Ambient temperature (operation)	-40 °C ... 85 °C (dependent on the derating curve)
Ambient temperature (assembly)	-5 °C ... 50 °C

Standards and regulations

Standards/specifications	IEC 62852:2014/AMD1:2020
--------------------------	--------------------------

PV-C1F-C-HSG - Photovoltaic connector





1050771

<https://www.phoenixcontact.com/us/products/1050771>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1050771>

 UL Recognized Approval ID: E477377-20230908				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	1500 V	50 A	14 - 10	-

 TÜV Rheinland Approval ID: R 60159495-0001				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	1500 V	40 A	-	2.5 - 6

PV-C1F-C-HSG - Photovoltaic connector



1050771

<https://www.phoenixcontact.com/us/products/1050771>

Classifications

ECLASS

ECLASS-13.0	27440107
ECLASS-15.0	27440107

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PV-C1F-C-HSG - Photovoltaic connector



1050771

<https://www.phoenixcontact.com/us/products/1050771>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Triphenyl phosphate(CAS: 115-86-6)
SCIP	151bb1c0-f06b-416f-be4b-0f0d48230e33

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com