

# AXL F EX IS AI8 HART XC 1F - Analog module



1052432

<https://www.phoenixcontact.com/us/products/1052432>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Axioline F, Analog input module, Active analog inputs: 8 (HART), 4 mA ... 20 mA, connection technology: 2-conductor, transmission speed in the local bus: 100 Mbps, Extreme conditions version, intrinsically safe, HART functionality, degree of protection: IP20, including bus base module and Axioline F connectors

## Product description

The module is an Axioline F I/O module for use in the Axioline F modular I/O system. The module is a modular I/O device that can be affixed to the Axioline F local bus, to communicate I/O data up to the Axioline F controller or bus coupler, which forms the head of the station. As an intrinsic safety I/O module, this device allows direct connection from intrinsically safe field I/Os to the terminals of the module. The analog input I/O module with HART capabilities collects analog input and HART data from the field I/O terminals and makes this information available to the controller / bus coupler through the Axioline F local bus. The active analog input module allows the connection of up to eight HART enabled, passive analog input signals.

## Your advantages

- Active analog input module
- Sources power for up to 8 HART enabled, passive analog input signals
- Cyclic access to PV, SV, TV, QV, and Loop Current
- Current range: 4 mA ... 20 mA
- Intrinsically safe analog inputs with connection to Zone 1, Zone 0 or Division 1
- Can be used under extreme ambient conditions
- Extended temperature range of -40 °C ... +70 °C (see "Tested successfully: use under extreme ambient conditions" in the data sheet)

## Commercial data

Item number	1052432
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR02
Product key	DRI2E7
GTIN	4055626676715
Weight per piece (including packing)	398.7 g
Weight per piece (excluding packing)	380 g
Customs tariff number	85176200
Country of origin	US

# AXL F EX IS AI8 HART XC 1F - Analog module




1052432

<https://www.phoenixcontact.com/us/products/1052432>

## Technical data

### Dimensions

Dimensional drawing	
Width	53.6 mm
Height	129.9 mm
Depth	77.1 mm
Note on dimensions	The depth applies when a TH 35-7.5 DIN rail is used (in accordance with EN 60715).

### Notes

Note on application	
Note on application	Only for industrial use
Utilization restriction	
EMC note	EMC: class A product, see manufacturer's declaration in the download area
Utilization restriction	
CCCex note	Use in potentially explosive areas is not permitted in China.

### Interfaces

Axioline F local bus	
Number of interfaces	2
Connection method	Bus base module
Transmission speed	100 Mbps

### System properties

Module	
Input address area	48 Byte
Output address area	0 Byte
Required parameter data	27 Byte
Required configuration data	6 Byte

### Input data

Analog:	
Input name	Active analog inputs

# AXL F EX IS AI8 HART XC 1F - Analog module



1052432

<https://www.phoenixcontact.com/us/products/1052432>

Description of the input	HART enabled, active analog input signals
Number of inputs	8 (HART)
A/D conversion time	500 $\mu$ s
Connection method	Push-in connection
Connection technology	2-conductor
Note regarding the connection technology	shielded, twisted pair
Current input signal	4 mA ... 20 mA
Input resistance current input	100 $\Omega$ (typical)
A/D converter resolution	12 bit
Data formats	Inline, S7-compatible, standard formatting
Input filter	25 Hz
Filtering	RFI filtering / passive TP 2nd order
Limit frequency (3 dB)	15 Hz
Measured value representation	16 bits (15 bits + sign bit)
Protective circuit	Polarity reversal protection of the inputs

## Product properties

Product type	I/O component
Product family	Axioline F
Type	block modular
Mounting position	any (no temperature derating)
Scope of supply	including bus base module and Axioline F connectors
Special properties	Extreme conditions version
	intrinsically safe
	HART functionality

## Insulation characteristics

Overvoltage category	II (IEC 60664-1, EN 60664-1)
Pollution degree	2 (IEC 60664-1, EN 60664-1)

## Electrical properties

Maximum power dissipation for nominal condition	2.51 W
---	--------

### Potentials: Axioline F local bus supply ( $U_{BUS}$ )

Supply voltage	5 V DC (via bus base module)
Current draw	max. 60 mA
	typ. 40 mA

### Potentials: Supply for analog modules ( $U_A$ )

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 240 mA
Protective circuit	Surge protection; electronic (35 V, 0.5 s)
	Reverse polarity protection; Polarity protection diode
	Transient protection; Suppressor diode

# AXL F EX IS AI8 HART XC 1F - Analog module



1052432

<https://www.phoenixcontact.com/us/products/1052432>

## Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply of the local bus ( $U_{BUS}$ ) / 24 V supply (I/Os)	500 V AC, 60 Hz, 1 min
Test voltage: 5 V supply of the local bus ( $U_{BUS}$ ) / functional ground	500 V AC, 60 Hz, 1 min
Test voltage: 5 V supply of the local bus ( $U_{BUS}$ ) / analog inputs	1500 V AC, 60 Hz, 1 min
Test voltage: 24 V supply (I/O) / functional ground	500 V AC, 60 Hz, 1 min
Test voltage: 24 V supply (I/O) / analog inputs	1500 V AC, 60 Hz, 1 min
Test voltage: Analog inputs / functional ground	500 V AC, 60 Hz, 1 min

## Connection data

### Connection technology

Connection name	Axioline F connector
Note on the connection method	Please observe the information provided on conductor cross-sections in the "Axioline F: system and installation" user manual.

### Axioline F connector

Connection method	Push-in connection
Note on the connection method	Please observe the information provided on conductor cross-sections in the "Axioline F: system and installation" user manual.
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C (Standard) -40 °C ... 70 °C (Extended, see section "Tested successfully: use under extreme ambient conditions" in the data sheet.)
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Approvals

### ATEX

Identification	II 3(1) G Ex ec [ia Ga] IIC T4 Gc II (1) D [Ex ia Da] IIIC
Certificate	DEMKO 20 ATEX 2370X

# AXL F EX IS AI8 HART XC 1F - Analog module



1052432

<https://www.phoenixcontact.com/us/products/1052432>

## IECEX

Identification	Ex ec [ia Ga] IIC T4 Gc [Ex ia Da] IIIC
Certificate	IECEX UL 20.0044X

## UKCA Ex (UKEX)

Identification	II 3(1) G Ex ec [ia Ga] IIC T4 Gc II (1) D [Ex ia Da] IIIC
Certificate	UL22UKEX2508X

## UL, USA/Canada

Identification	cULus
Certificate	E238705

## UL Ex, USA / Canada

Identification	Class I, Division 2, Groups A, B, C, D, T4
	Intrinsically safe connections to: Class I, Groups A, B, C, D; Class II, Groups E, F, G; Class III; [Ex ia] Haz loc
	Class I, Zone 2, AEx ec [ia Ga] IIC T4 Gc
	[AEx ia Da] IIIC
	Ex ec [ia Ga] IIC T4 Gc
Certificate	[Ex ia Da] IIIC
	E196811

## CCC / China-Ex

Identification	Ex ec [ia Ga] IIC T4 Gc
	[Ex ia Da] IIIC

## Ex data

UL, USA / Canada	Ind. Cont. Eq. (E238705) also Listed Ind. Cont. Eq. for haz. loc. E196811 Install in: Class I, Div. 2, Groups A, B, C, D T4 Intrinsically safe outputs for: Class I, Groups A, B, C, D; Class II, Groups E, F, G; Class III; [Ex ia] Haz loc Class I, Zone 2, AEx ec [ia Ga] IIC T4 Gc [AEx ia Da] IIIC Ex ec [ia Ga] IIC T4 Gc [Ex ia Da] IIIC
------------------	---

## Mounting

Mounting type	DIN rail mounting
Mounting position	any (no temperature derating)

## Ex data

### Safety data

Max. output voltage $U_o$	24.8 V
Max. output current $I_o$	85.8 mA
Max. output power $P_o$	532 mW
Safety-related maximum voltage $U_m$	250 V

# AXL F EX IS AI8 HART XC 1F - Analog module



1052432

<https://www.phoenixcontact.com/us/products/1052432>

A, B / IIC: Max. external inductivity $L_o$ / Max. external capacitance $C_o$	2.95 mH / 0.113 $\mu$ F
C/IIB, IIIC: Max. external inductivity $L_o$ / Max. external capacitance $C_o$	18.95 mH / 0.86 $\mu$ F
D/IIA, E, F, G, Class III: Max. external inductivity $L_o$ / Max. external capacitance $C_o$	30.95 mH / 3.05 $\mu$ F



# AXL F EX IS AI8 HART XC 1F - Analog module

1052432

<https://www.phoenixcontact.com/us/products/1052432>

## Drawings

Dimensional drawing




Dimensional drawing

Schematic diagram

**Safe area**

Class I, Division 2 , Groups ABCD, T4  
 Class I, Zone 2, IIC, T4  
 Zone 2, IIC, T4

Class I/II/III, Division 1, Groups ABCDEFG  
 Class I, Zone 0, IIC  
 Class II, Zone 20, IIIC  
 Zone 0, IIC  
 Zone 20, IIC



# AXL F EX IS AI8 HART XC 1F - Analog module



1052432

<https://www.phoenixcontact.com/us/products/1052432>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1052432>



**cULus Listed**

Approval ID: E238705



**IECEX**

Approval ID: IECEX UL 20.0044X



**cUL Listed**

Approval ID: FILE E196811



**UL Listed**

Approval ID: FILE E196811



**ATEX**

Approval ID: DEMKO 20 ATEX 2370X



**CCC**

Approval ID: 2021122316114727



**UKCA-EX**

Approval ID: UL22UKEX2508X

# AXL F EX IS AI8 HART XC 1F - Analog module



1052432

<https://www.phoenixcontact.com/us/products/1052432>

## Classifications

### ECLASS

ECLASS-13.0	27242601
ECLASS-15.0	27242601

### ETIM

ETIM 10.0	EC001596
-----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

# AXL F EX IS AI8 HART XC 1F - Analog module



1052432

<https://www.phoenixcontact.com/us/products/1052432>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0f5c460a-add9-4fd4-9bc8-cffcdf461953

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)