VS-FP-SD-GB-RJ456A-BUBU - Data front plate

1054544

https://www.phoenixcontact.com/us/products/1054544

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective contact socket, plastic, for Great Britain, including RJ45 gender changer (female/female, shielded), CAT6A

Commercial data

Item number	1054544
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF70
Product key	AF7EBX
GTIN	4055626689296
Weight per piece (including packing)	101.2 g
Weight per piece (excluding packing)	101.2 g
Customs tariff number	85366990
Country of origin	LV

Technical data

Product properties

Product type	Data front plate
Number of positions	8
Country ID	Great Britain


Electrical properties

Rated voltage (III/3)	250 V (Socket)
	max. 30 V AC (RJ45)
	max. 42.4 V DC (RJ45)
Rated current	13 A (Socket)
Nominal current I_N	max. 175 mA (RJ45)
Transmission speed	10 Gbps (Class EA (ISO/IEC 11801:2002), (EN 50173-1))

Connection data

Connection method	Screw connection

Dimensions

Dimensional drawing	
Width	50.7 mm
Height	43 mm
Length	87.5 mm

Material specifications

Material	Die-cast zinc, nickel-plated (RJ45)
Material Housing	PBT (Front plate)
Material	(Socket, labeling field)

Connector

Contact insert design	with 1x RJ45 Socket/socket, Cat 6, classEA (ISO/IEC 11801:2002), (EN 50173-1)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	>= 750 (RJ45)

Environmental and real-life conditions

Ambient conditions


Degree of protection	IP20 (Front)
Ambient temperature (operation)	-5 °C ... 50 °C

Mounting

Assembly note	Shroud connection: M4 threaded pin, tightening torque: 0.8 Nm ... 1.0 Nm

Drawings

Dimensional drawing



Dimensional drawing

Classifications

ECLASS

ECLASS-13.0	27182806
ECLASS-15.0	27182806

ETIM

ETIM 10.0	EC000456

UNSPSC

UNSPSC 21.0	39121300

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	8.137 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com