

TTC-6P-1X2-EX-24DC-UT-I - Surge protection device



1065312

<https://www.phoenixcontact.com/us/products/1065312>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protection, consisting of protective plug and base element, with integrated status indicator for a 2-wire floating Ex i signal circuit, e.g., 0(4) mA ... 20 mA current loop, HART-compatible. Can be used in safety-related circuits up to SIL 3.

Your advantages

- Space-saving and cost-saving with a narrow overall width of just 6 mm
- Continuous monitoring of protective devices, plus mechanical status indicator with optional remote signaling
- Finding the right product for all possible requirements in MCR applications is easy, thanks to the complete range of products with customized features
- Easy testing and documentation with CHECKMASTER 2 with pluggable protective modules
- The signal is not influenced during maintenance work, thanks to the impedance-neutral insertion and removal of protective plugs

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1065312 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | CL23 |
| Product key | CL2163 |
| GTIN | 4055626725390 |
| Weight per piece (including packing) | 66 g |
| Weight per piece (excluding packing) | 39.46 g |
| Customs tariff number | 85363010 |
| Country of origin | DE |

TTC-6P-1X2-EX-24DC-UT-I - Surge protection device



1065312

<https://www.phoenixcontact.com/us/products/1065312>

Technical data

Product properties

| | |
|-------------------------|---|
| Product type | Surge protection for MCR technology |
| Product family | TERMITRAB complete |
| IEC test classification | C1 |
| | C2 |
| | C3 |
| | D1 |
| Type | DIN rail module, two-section, divisible |
| Wire pairs per module | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree | 2 |

Electrical properties

| | |
|-----------------------|---------|
| Nominal voltage U_N | 24 V DC |
|-----------------------|---------|

Connection data

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Screw thread | M3 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Ex data

| | |
|---------------------------------|--|
| Maximum inner capacitance C_i | negligible |
| Max. internal inductance L_i | negligible |
| Max. input current I_i | 400 mA (T4 / -40 °C ... +50 °C) |
| | 250 mA (T4 / -40 °C ... +70 °C) |
| | 350 mA (T6 / -40 °C ... +35 °C) |
| | 100 mA (T6 / -40 °C ... +70 °C) |
| Max. input voltage U_i | 30 V DC |
| Insulation voltage to ground | > 180 V DC |
| Ambient temperature (operation) | -40 °C ... 70 °C (with current derating) |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing | |
|---------------------|--|

TTC-6P-1X2-EX-24DC-UT-I - Surge protection device



1065312

<https://www.phoenixcontact.com/us/products/1065312>

| | |
|--------|--------------------------------|
| Width | 6.2 mm +0.1 mm |
| Height | 105.8 mm |
| Depth | 100 mm (incl. DIN rail 7.5 mm) |

Material specifications

| | |
|--|-----------------------|
| Color | blue (RAL 5015) |
| | light gray (RAL 7035) |
| Flammability rating according to UL 94 | V-0 |
| Insulating material | PBT |
| Housing material | PBT |

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Protective circuit

| | |
|---|--|
| Direction of action | Line-Line & Line-Signal Ground/Shield & optional Signal Ground/Shield-Earth Ground |
| Nominal voltage U_N | 24 V DC |
| Maximum continuous operating voltage U_C | 30 V DC |
| Rated current | 600 mA (40 °C) |
| Operating effective current I_C at U_C | $\leq 5 \mu\text{A}$ |
| Protective conductor current I_{PE} | $\leq 1 \mu\text{A}$ |
| Nominal discharge current I_n (8/20) μs (line-line) | 5 kA |
| Nominal discharge current I_n (8/20) μs (line-ground) | 5 kA |
| Pulse discharge current I_{imp} (10/350) μs (line-line) | 0.5 kA |
| Pulse discharge current I_{imp} (10/350) μs (line-earth) | 0.5 kA |
| Total discharge current I_{Total} (8/20) μs | 10 kA |
| Voltage protection level U_p (line-line) | $\leq 55 \text{ V}$ (C1 - 1 kV / 500 A) |
| | $\leq 65 \text{ V}$ (C2 - 10 kV / 5 kA) |
| | $\leq 55 \text{ V}$ (C3 - 100 A) |
| Voltage protection level U_p (line-earth) | $\leq 900 \text{ V}$ (C1 - 1 kV / 500 A) |
| | $\leq 1.05 \text{ kV}$ (C2 - 10 kV / 5 kA) |
| | $\leq 1.4 \text{ kV}$ (C3 - 100 A) |
| Voltage protection level U_p static (line-line) | $\leq 50 \text{ V}$ (C1 - 1 kV / 500 A) |
| | $\leq 65 \text{ V}$ (C2 - 10 kV / 5 kA) |
| Voltage protection level U_p static (line-earth) | $\leq 900 \text{ V}$ (C1 - 1 kV / 500 A) |
| | $\leq 1.05 \text{ kV}$ (C2 - 10 kV / 5 kA) |
| Response time t_A (line-line) | $\leq 1 \text{ ns}$ |
| Response time t_A (line-earth) | $\leq 100 \text{ ns}$ |
| Input attenuation aE, sym. | typ. 0.3 dB ($\leq 250 \text{ kHz}$ / 150 Ω) |
| Cut-off frequency f_g (3 dB), sym. in 150 Ω system | typ. 940 kHz |
| Capacity (Core-Core) | typ. 2 nF |
| Resistance per path | 1.65 $\Omega \pm 20 \%$ |

TTC-6P-1X2-EX-24DC-UT-I - Surge protection device



1065312

<https://www.phoenixcontact.com/us/products/1065312>

| | |
|---------------------------------|-------------------|
| Surge protection fault message | optical |
| Max. required back-up fuse | 630 mA (FF) |
| Impulse durability (line-line) | C1 - 1 kV / 500 A |
| | C2 - 10 kV / 5 kA |
| | C3 - 100 A |
| Impulse durability (line-earth) | C1 - 1 kV / 500 A |
| | C2 - 10 kV / 5 kA |
| | C3 - 100 A |
| | D1 - 500 A |
| Pulse reset time (line-line) | ≤ 700 ms |
| Pulse reset time (line-earth) | ≤ 30 ms |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Altitude | ≤ 2000 m (amsl) |
| Permissible humidity (operation) | 5 % ... 95 % |

Approvals

Conformity/Approvals

| | |
|------------------|--|
| UL, USA / Canada | Class I, Div. 2, Groups A, B, C, D T4A |
|------------------|--|

Standards and regulations

| | |
|--------------------------|-------------|
| Standards/specifications | EN 60079-0 |
| Note | 2018 |
| Standards/specifications | EN 60079-11 |
| Note | 2012 |

EN 61643-21

| | |
|--------------------------|---|
| Standards/specifications | EN 61643-21 |
| Note | 2001 + A1:2009 + A2:2013 |
| Standards/specifications | IEC 60079-0 |
| Note | 2017 |
| Standards/specifications | IEC 60079-11 |
| Note | 2008 |
| Standards/specifications | IEC 61643-21 |
| Note | 2000 + corrigendum 2001 + A1:2008, modified + A2:2012 |

Mounting

| | |
|---------------|--------------------------|
| Mounting type | DIN rail: TH 35 - 7.5 mm |
|---------------|--------------------------|

TTC-6P-1X2-EX-24DC-UT-I - Surge protection device



1065312

<https://www.phoenixcontact.com/us/products/1065312>

Drawings

Dimensional drawing



Schematic diagram

| TTC-6P-1x2-...-I | | | | | | | | | |
|------------------|--------------------------|---------------------------|--------------------------|-------|--------------------------|----------------------------|------|--------------------------|-------|
| Category | 1oo1 architecture, HFT=0 | | | | 1oo2 architecture, HFT=1 | | | | |
| | PFD _{AVG} | PFH | Used budget of SIL 2 SIF | | PFD _{AVG} | PFH | CCF | Used budget of SIL 3 SIF | |
| | | | PFD _{AVG} | PFH | | | | PFD _{AVG} | PFH |
| | 3.88·10 ⁻⁵ | 6.90·10 ⁻⁹ 1/h | 0.4 % | 0.7 % | 1.94·10 ⁻⁶ | 3.45·10 ⁻¹⁰ 1/h | 5 % | 0.2 % | 0.3 % |
| | | | | | 3.88·10 ⁻⁶ | 6.90·10 ⁻¹⁰ 1/h | 10 % | 0.4 % | 0.7 % |

Calculation based on exida report, Phoenix Contact 16/06-072 R022 V4R2
 exida Profile 1, FMEDA Analysis 2, T_{proof}: 1 year, MT: 10 years, MTTR: 24 hours, PTC: 99%
 Used standards
 IEC/EN 61508, edition 2010 (device specific)
 IEC/EN 61511, edition 2016 + COR1:2016 + A1:2017 (system specific)

Functional safety scenarios

Diagram



Derating for non-Ex applications


TTC-6P-1X2-EX-24DC-UT-I - Surge protection device



1065312

<https://www.phoenixcontact.com/us/products/1065312>

Circuit diagram



1065312

<https://www.phoenixcontact.com/us/products/1065312>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1065312>



DNV GL

Approval ID: TAE000027G



UL Listed

Approval ID: FILE E 138168

UAE-RoHS

Approval ID: 22-06-16192

Functional Safety

Approval ID: 16-06-072 R022 V4R3



UL Listed

Approval ID: FILE E 138168



cUL Listed

Approval ID: FILE E 333250



UL Listed

Approval ID: FILE E 333250

INMETRO

Approval ID: 19.0077 X



NEPSI-EX

Approval ID: GYJ20.1114X



CCC

Approval ID: 2020322316000780



UKCA-EX

Approval ID: DEKRA 23UKEX0110X

TTC-6P-1X2-EX-24DC-UT-I - Surge protection device



1065312

<https://www.phoenixcontact.com/us/products/1065312>



cULus Listed

Approval ID: File E 333250



IECEX

Approval ID: IECEX BVS 16.0090X



ATEX

Approval ID: BVS 16 ATEX E 125 X

1065312

<https://www.phoenixcontact.com/us/products/1065312>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27171502 |
| ECLASS-15.0 | 27171502 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001466 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

1065312

<https://www.phoenixcontact.com/us/products/1065312>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| | Lead(CAS: 7439-92-1) |
| SCIP | ac1af30a-ed6b-45cc-ac29-cc6065a9f322 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 1.421 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com